



LED PAR38

12PAR38/LED/840/F25/DIM/ULW/120V 6/1FB

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.


Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	25000X
Technical Type	12-90W
Light Technical	
Color Code	840 [CCT of 4000K]
Beam Angle (Nom)	25 °
Luminous Flux (Nom)	900 lm
Luminous Intensity (Nom)	4100 cd
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	75.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	12 W
Lamp Current (Nom)	112 mA
Wattage Equivalent	90 W

Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.8
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	66 °C
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Efficiency Label (EEL)	Not applicable
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	12PAR38/LED/840/F25/DIM/ULW/120V 6/1FB
EAN/UPC - Product	046677529642
Order code	929001319704
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929001319704
Net Weight (Piece)	0.385 kg

LED PAR38


Dimensional drawing




Classic PAR38 120V 11-90W 900lm 25D 4000

Product	D	C
12PAR38/LED/840/F25/DIM/ULW/120V 6/1FB	122 mm	134 mm


Photometric data



12-90W E26 PAR38 25D 840 4000K



12-90W E26 PAR38





Product Reference: E1 Photo Lighting E1 Page 17

12-90W E26 PAR38 25D 840 4000K

LED PAR38

Lifetime



14-120W E26 PAR38

14-120W E26 PAR38

