



MASTER VALUE LEDs pot LV

MASTER LED spot VLE D 5.5-35W MR16 840 36D

Delivering a warm, halogen-like accent beam, MASTER LEDspot LV is an ideal retrofit solution for spot and general lighting applications in the hospitality industry. It is particularly suited to public areas such as receptions, lobbies, corridors, stairwells and washrooms, where the light is on all the time. The robustly designed MASTER LEDspot offers a choice of beam angles for a clearly defined beam spread. There is no UV or IR in the beam, making it suitable for illuminating heat-sensitive objects (food, organic materials, paintings, etc.). The patented intelligent driver enables broad compatibility with existing electromagnetic and electronic halogen transformers. The dimmable versions drive further efficiencies, while helping to create the desired atmosphere.

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights


Product data

General Information			
Cap-Base	GU5.3 [GU5.3]	Beam Angle (Nom)	36 degree(s)
Nominal lifetime	25,000 hour(s)	Luminous Flux	490 lm
Switching Cycle	50,000	Luminous Intensity (Nom)	1,100 cd
Lighting Technology	LED	Color Designation	Cool White (CW)
EU RoHS compliant	Yes	Correlated Color Temperature (Nom)	4000 K
		Luminous Efficacy (rated) (Nom)	89.09 lm/W
		Color Consistency	<6
		Color rendering index (CRI)	80
		LLMF At End Of Nominal Lifetime (Nom)	70 %
Light Technical			
Color Code	840 [CCT of 4000K]		


MASTER VALUE LEDspot LV

Luminous Flux in 90° Cone (Rated)	490 lm
Operating and Electrical	
Line Frequency	- Hz
Input Frequency	- Hz
Power Consumption	5.5 W
Lamp Current (Nom)	630 mA
Wattage Equivalent	35 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.8
Voltage (Nom)	ac Electronic 12 V
Temperature	
T-Case Maximum (Nom)	95 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]

Dimensional drawing




Photometric data



Accent Lighting Spots - MAS LED spot VLE D 5.5-35W MR16 840 36D

Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	7 kWh
EyeComfort	Yes
Product Data	
Order product name	MAS LED spot VLE D 5.5-35W MR16 840 36D
Full product name	MASTER LED spot VLE D 5.5-35W MR16 840 36D
Full product code	871869670827900
Order code	70827900
Material Nr. (12NC)	929001326102
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696708279
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696708286


Product	D	C
MAS LED spot VLE D 5.5-35W MR16 840 36D	50.5 mm	45 mm



Light Distribution Diagram - MAS LED spot VLE D 5.5-35W MR16 840 36D


MASTER VALUE LEDspot LV

Photometric data




Spectral Power Distribution Colour - MAS LED spot VLE D 5.5-35W MR16 840 36D

Lifetime



Life Expectancy Diagram - MAS LED spot VLE D 5.5-35W MR16 840 36D



Lumen Maintenance Diagram - MAS LED spot VLE D 5.5-35W MR16 840 36D

