



# MASTER VALUE LEDs pot LV

## MAS LED spot VLE D 5.5-35W MR16 840 60D

Philips MASTER VALUE MR16 is the series of Low Voltage (12VAC) Halogen MR16 replacements. Not only does it employ Philips' patented solution to guarantee the broadest possible compatibility with standard 12V Halogen electronic transformers. It also delivers beam intensity which is equivalent to the 50W Philips Halogen MR16 lamps. The form-factor of Philips MASTER Value LED MR16 guarantees a 100% form on the back-side of the lamp (exact form with Halogen lamps.)

### Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

### Product data

General Information	
Cap-Base	GU5.3 [GU5.3]
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	840 [CCT of 4000K]
Beam Angle (Nom)	60 degree(s)
Luminous Flux	490 lm
Luminous Intensity (Nom)	550 cd
Color Designation	Cool White (CW)

Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	89.09 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	490 lm

Operating and Electrical	
Line Frequency	- Hz
Input Frequency	- Hz
Power Consumption	5.5 W
Lamp Current (Nom)	630 mA
Wattage Equivalent	35 W

MASTER VALUE LEDspot LV


Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.8
Voltage (Nom)	ac Electronic 12 V
Temperature	
T-Case Maximum (Nom)	95 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]
Approval and Application	
Suitable For Accent Lighting	Yes

Dimensional drawing

Energy Consumption kWh/1000 h	7 kWh
EyeComfort	Yes
Product Data	
Order product name	MAS LED spot VLE D 5.5-35W MR16 840 60D
Full product name	MAS LED spot VLE D 5.5-35W MR16 840 60D
Full product code	871869670833000
Order code	929001326402
Material Nr. (12NC)	929001326402
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696708330
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696708347

Product	D	C
MAS LED spot VLE D 5.5-35W MR16 840 60D	50.5 mm	45 mm

Photometric data




Accent Lighting Spots - MAS LED spot VLE D 5.5-35W MR16 840 60D

Light Distribution Diagram - MAS LED spot VLE D 5.5-35W MR16 840 60D


MASTER VALUE LEDspot LV

Photometric data




Spectral Power Distribution Colour - MAS LED spot VLE D 5.5-35W MR16 840 60D

Lifetime



Life Expectancy Diagram - MAS LED spot VLE D 5.5-35W MR16 840 60D



Lumen Maintenance Diagram - MAS LED spot VLE D 5.5-35W MR16 840 60D

