



Classic filament LEDbulbs

CLA LEDBulb D 5.5-40W A60 E27 827 CL

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data


General Information		Power Consumption	
Cap base	E27 [E27]	Lamp current (nom.)	38 mA
Nominal lifetime	15,000 h	Wattage equivalent	40 W
Switching Cycle	20,000	Starting time (nom.)	0.5 s
Lighting Technology	LED	Warm-up time to 60% light	0.5 s
EU RoHS compliant	Yes	Power Factor (Fraction)	0.7
Light Technical		Voltage (nom.)	220-240 V
Colour Code	827 [CCT of 2700K]	Temperature	
Luminous Flux	470 lm	T-Case maximum (nom.)	50 °C
Colour designation	Warm White (WW)	Controls and Dimming	
Correlated Colour Temperature	2700 K	Dimmable	Yes
Luminous efficacy (rated) (nom.)	85.00 lm/W	Mechanical and Housing	
Colour consistency	<6	Lamp Finish	Clear
Colour rendering index (CRI)	80	Bulb shape	A60 [A 60 mm]
LLMF at end of nominal lifetime (nom.)	70 %	Approval and Application	
Operating and Electrical		Energy consumption kWh/1,000 hours	6 kWh
Line Frequency	50 to 60 Hz		
Input frequency	50 to 60 Hz		

Classic filament LEDbulbs

EyeComfort	Yes
Product Data	
Order product name	CLA LEDBulb D 5.5-40W A60 E27 827 CL
Full product name	CLA LEDBulb D 5.5-40W A60 E27 827 CL
Full EOC	871869670940500
Order code	70940500


Material no. (12 NC)	929001331002
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696709405
Numerator – packs per outer box	10
EAN/UPC - Case	8718696709412

Dimensional drawing




Product	D	C
CLA LEDBulb D 5.5-40W A60 E27 827 CL	60 mm	104 mm


Photometric data



Spectral Power Distribution Colour - CLA LEDBulb D 5.5-40W A60 E27 827 CL




General uniform lighting - CLA LEDBulb D 5.5-40W A60 E27 827 CL




Light Distribution Diagram - CLA LEDBulb D 5.5-40W A60 E27 827 CL

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - CLA LEDBulb D 5.5-40W A60 E27 827 CL



Lumen Maintenance Diagram - CLA LEDBulb D 5.5-40W A60 E27 827 CL

