



Classic filament LEDbulbs

CLA LEDBulb D 5-40W A60 B22 827 CL

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data


General Information			
Cap-Base	B22 [B22]	Power Consumption	5,5 W
Nominal lifetime	15,000 hour(s)	Lamp Current (Nom)	38 mA
Switching Cycle	20,000	Wattage Equivalent	40 W
Lighting Technology	LED	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
Light Technical		Power Factor (Fraction)	0.7
Color Code	827 [CCT of 2700K]	Voltage (Nom)	220-240 V
Luminous Flux	470 lm	Temperature	
Color Designation	Warm White (WW)	T-Case Maximum (Nom)	50 °C
Correlated Color Temperature (Nom)	2700 K	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	85.00 lm/W	Dimmable	Yes
Color Consistency	<6	Mechanical and Housing	
Color rendering index (CRI)	80	Bulb Finish	Clear
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Shape	A60 [A 60mm]
Operating and Electrical			
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz		

Classic filament LEDbulbs

Approval and Application	
Energy Consumption kWh/1000 h	6 kWh
Product Data	
Order product name	CLA LEDBulb D 5-40W A60 B22 827 CL
Full product name	CLA LEDBulb D 5-40W A60 B22 827 CL
Full product code	871869670942900
Order code	929001331102


Material Nr. (12NC)	929001331102
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696709429
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696709436

Dimensional drawing




Product	D	C
CLA LEDBulb D 5-40W A60 B22 827 CL	60 mm	102 mm

Photometric data



Spectral Power Distribution Colour - CLA LEDBulb D 5-40W A60 B22 827 CL


General uniform lighting - CLA LEDBulb D 5-40W A60 B22 827 CL




Light Distribution Diagram - CLA LEDBulb D 5-40W A60 B22 827 CL

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - CLA LEDBulb D 5-40W A60 B22 827 CL



Lumen Maintenance Diagram - CLA LEDBulb D 5-40W A60 B22 827 CL

