



# Classic filament LEDbulbs

## CLA LEDBulb D 8-60W A60 E27 827 CL

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

### Product data

General Information	
Cap base	E27 [ E27]
RoHS mark	RoHS mark
Nominal lifetime (nom.)	15000 h
Switching cycle	20000X
Technical type	8-60W
Light Technical	
Colour Code	827 [ CCT of 2,700 K]
Lamp Luminous Flux 25°C EL (Nom)	806 lm
Lamp Luminous Flux (Nom)	806 lm
Colour Designation	Warm white (WW)
Colour Temperature, horizontal (Nom)	2700 K
Lamp Luminous Efficacy EM (Nom)	100.00 lm/W
Colour consistency	<6
Colour Rendering Index,horiz (Nom)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz


Power (Rated) (Nom)	8 W
Lamp current (nom.)	52 mA
Wattage equivalent	60 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	55 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb finish	Clear
Approval and Application	
Energy efficiency label (EEL)	A+

## Classic filament LEDbulbs

Energy Consumption kWh/1000 h	8 kWh
<b>Product Data</b>	
Full product code	871869670944300
Order product name	CLA LEDBulb D 8-60W A60 E27 827 CL
EAN/UPC – product	8718696709443
Order code	929001331202

Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001331202
Net weight (piece)	0.030 kg


### Dimensional drawing




Bulb A60 230V7.5-60W 806lm 2700K D Clear

Product	D	C
CLA LEDBulb D 8-60W A60 E27 827 CL	60 mm	104 mm


### Photometric data



LEDbulb, Bulb A21 14W, 18W 2200-2700K



LEDbulb 60W E27 827 CL A60 D




LEDbulb 40W E27 827 CL A60 D

## Classic filament LEDbulbs

### Lifetime



LEDbulb 40W E27 827 CL A60 D



LEDbulb 40W E27 827 CL A60 D

