

Classic filament LEDbulbs

CLA LEDBulb D 8-60W A60 B22 827 CL

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap base	B22 [B22]
Nominal lifetime	15,000 h
Switching Cycle	20,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Colour Code	827 [CCT of 2700K]
Luminous Flux	806 lm
Colour designation	Warm White (WW)
Correlated Colour Temperature	2700 K
Luminous efficacy (rated) (nom.)	100.00 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz

Power Consumption	8 W
Lamp current (nom.)	52 mA
Wattage equivalent	60 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (nom.)	220-240 V

Temperature	
T-Case maximum (nom.)	55 °C


Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	A60 [A 60 mm]


Classic filament LEDbulbs

Approval and Application	
Energy consumption kWh/1,000 hours	8 kWh
Product Data	
Order product name	CLA LEDBulb D 8-60W A60 B22 827 CL
Full product name	CLA LEDBulb D 8-60W A60 B22 827 CL
Full EOC	871869670946700
Order code	70946700


Dimensional drawing



Photometric data




Spectral Power Distribution Colour - CLA LEDBulb D 8-60W A60 B22 827 CL



Light Distribution Diagram - CLA LEDBulb D 8-60W A60 B22 827 CL

Material no. (12 NC)	929001331302
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696709467
Numerator – packs per outer box	10
EAN/UPC - Case	8718696709474


Product	D	C
CLA LEDBulb D 8-60W A60 B22 827 CL	60 mm	102 mm




General uniform lighting - CLA LEDBulb D 8-60W A60 B22 827 CL

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - CLA LEDBulb D 8-60W A60 B22 827 CL



Lumen Maintenance Diagram - CLA LEDBulb D 8-60W A60 B22 827 CL

