



# Classic filament LED candles and lusters

## CLA LEDCandle D 5-40W B35 B22 827 CL

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.


### Product data

<b>General Information</b>			
Cap-Base	B22 [B22]	Power Consumption	5 W
Nominal lifetime	15,000 hour(s)	Lamp Current (Nom)	38 mA
Switching Cycle	20,000	Wattage Equivalent	40 W
Lighting Technology	LED	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.7
		Voltage (Nom)	220-240 V
<b>Light Technical</b>			
Color Code	827 [CCT of 2700K]	<b>Temperature</b>	
Luminous Flux	470 lm	T-Case Maximum (Nom)	60 °C
Color Designation	Warm White (WW)	<b>Controls and Dimming</b>	
Correlated Color Temperature (Nom)	2700 K	Dimmable	Yes
Luminous Efficacy (rated) (Nom)	94.00 lm/W	<b>Mechanical and Housing</b>	
Color Consistency	<6	Bulb Finish	Clear
Color rendering index (CRI)	80	Bulb Shape	B35 [B 35mm]
LLMF At End Of Nominal Lifetime (Nom)	70 %		
<b>Operating and Electrical</b>			
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz		


Classic filament LED candles and lusters

Approval and Application	
Energy Consumption kWh/1000 h	5 kWh
Product Data	
Order product name	CLA LEDCandle D 5-40W B35 B22 827 CL
Full product name	CLA LEDCandle D 5-40W B35 B22 827 CL
Full product code	871869670984900
Order code	929001332202

Dimensional drawing




Photometric data




Spectral Power Distribution Colour - CLA LEDCandle D 5-40W B35 B22 827 CL

Material Nr. (12NC)	929001332202
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696709849
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696709856

Product	D	C
CLA LEDCandle D 5-40W B35 B22 827 CL	35 mm	97 mm




General uniform lighting - CLA LEDCandle D 5-40W B35 B22 827 CL




Light Distribution Diagram - CLA LEDCandle D 5-40W B35 B22 827 CL

Classic filament LED candles and lusters

Lifetime



Life Expectancy Diagram - CLA LEDCandle D 5-40W B35 B22 827 CL



Lumen Maintenance Diagram - CLA LEDCandle D 5-40W B35 B22 827 CL

