



# MASTER Value Decorative LED bulbs

## CLA LEDBulb D 7.5-48W A60 E27 820 GOLD

The new Deco collection transforms your home with a perfect blend of warm white light and a lean, minimalistic lighting experience. With long lifetime, up to 90% energy savings, no flickering and an instant full-level brightness, you will also enjoy soft and evenly distributed light with that trendy and stylish charm for a welcoming harmony in your space.

### Product data


General Information	
Cap base	E27 [E27]
Nominal lifetime	15,000 h
Switching Cycle	20,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Colour Code	820 [CCT of 2000K]
Luminous Flux	610 lm
Colour designation	Flame
Correlated Colour Temperature	2000 K
Luminous efficacy (rated) (nom.)	81.33 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz

Power Consumption	7.5 W
Lamp current (nom.)	36 mA
Wattage equivalent	48 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (nom.)	220-240 V
Temperature	
T-Case maximum (nom.)	55 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Lamp Finish	Amber
Bulb shape	A60 [A 60 mm]

MASTER Value Decorative LED bulbs


Approval and Application	
Energy consumption kWh/1,000 hours	8 kWh
Product Data	
Order product name	CLA LEDBulb D 7.5-48W A60 E27 820 GOLD
Full product name	CLA LEDBulb D 7.5-48W A60 E27 820 GOLD
Full EOC	871869670956600
Order code	70956600

Dimensional drawing




Product	D	C
CLA LEDBulb D 7.5-48W A60 E27 820 GOLD	60 mm	104 mm


Photometric data



General uniform lighting - CLA LEDBulb D 7.5-48W A60 E27 820 GOLD




Spectral Power Distribution Colour - CLA LEDBulb D 7.5-48W A60 E27 820 GOLD




Light Distribution Diagram - CLA LEDBulb D 7.5-48W A60 E27 820 GOLD

MASTER Value Decorative LED bulbs

Lifetime



Life Expectancy Diagram - CLA LEDBulb D 7.5-48W A60 E27 820 GOLD



Lumen Maintenance Diagram - CLA LEDBulb D 7.5-48W A60 E27 820 GOLD

