



Classic filament LEDbulbs

CLA LEDBulb DT 8-60W ST64 E27 CL

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap base	E27 [E27]
Nominal lifetime	15,000 h
Switching Cycle	20,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Colour Code	822-827 [tunable warm white]
Luminous Flux	806 lm
Colour designation	Warm White (WW)
Luminous efficacy (rated) (nom.)	100.75 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	8 W

Lamp current (nom.)	41 mA
Wattage equivalent	60 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (nom.)	220-240 V

Temperature	
T-Case maximum (nom.)	55 °C

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	ST64


Approval and Application	
Energy consumption kWh/1,000 hours	8 kWh

Classic filament LEDbulbs

EyeComfort	Yes
Product Data	
Order product name	CLA LEDBulb DT 8-60W ST64 E27 CL
Full product name	CLA LEDBulb DT 8-60W ST64 E27 CL
Full EOC	871869670976400
Order code	70976400

Material no. (12 NC)	929001334002
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696709764
Numerator – packs per outer box	10
EAN/UPC – Case	8718696709771

Dimensional drawing




Product	D	C
CLA LEDBulb DT 8-60W ST64 E27 CL	64 mm	140 mm


Photometric data



Spectral Power Distribution Colour - CLA LEDBulb DT 8-60W ST64 E27 CL




General uniform lighting - CLA LEDBulb DT 8-60W ST64 E27 CL




Light Distribution Diagram - CLA LEDBulb DT 8-60W ST64 E27 CL

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - CLA LEDBulb DT 8-60W ST64 E27 CL



Lumen Maintenance Diagram - CLA LEDBulb DT 8-60W ST64 E27 CL

