



Classic filament LEDbulbs

CLA LEDBulb DT 8-60W ST64 E27 CL

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data


General Information		Lamp Current (Nom)	
Cap-Base	E27 [E27]		41 mA
Nominal lifetime	15,000 hour(s)	Wattage Equivalent	60 W
Switching Cycle	20,000	Starting Time (Nom)	0.5 s
Lighting Technology	LED	Warm-up time to 60% light	0.5 s
EU RoHS compliant	Yes	Power Factor (Fraction)	0.7
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	822-827 [tunable warm white]	T-Case Maximum (Nom)	55 °C
Luminous Flux	806 lm		
Color Designation	Warm White (WW)	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	100.75 lm/W	Dimmable	Yes
Color Consistency	<6		
Color rendering index (CRI)	80	Mechanical and Housing	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Finish	Clear
		Bulb Shape	ST64
Operating and Electrical		Approval and Application	
Line Frequency	50 to 60 Hz	Energy Consumption kWh/1000 h	8 kWh
Input Frequency	50 to 60 Hz		
Power Consumption	8 W		

Classic filament LEDbulbs

EyeComfort	Yes
Product Data	
Order product name	CLA LEDBulb DT 8-60W ST64 E27 CL
Full product name	CLA LEDBulb DT 8-60W ST64 E27 CL
Full product code	871869670976400
Order code	929001334002


Material Nr. (12NC)	929001334002
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696709764
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696709771

Dimensional drawing




Product	D	C
CLA LEDBulb DT 8-60W ST64 E27 CL	64 mm	140 mm

Photometric data



Spectral Power Distribution Colour - CLA LEDBulb DT 8-60W ST64 E27 CL



General uniform lighting - CLA LEDBulb DT 8-60W ST64 E27 CL



Light Distribution Diagram - CLA LEDBulb DT 8-60W ST64 E27 CL

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - CLA LEDBulb DT 8-60W ST64 E27 CL

Lumen Maintenance Diagram - CLA LEDBulb DT 8-60W ST64 E27 CL

