

# Ecofit Ledtubes T8

## Ecofit LEDtube 1500mm 20W 865 T8

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

### Product data


General Information		Starting time (nom.)	
Cap base	G13 [ Medium Bi-Pin Fluorescent]		0.5 s
RoHS mark	RoHS mark	Warm-up time to 60% light (nom.)	0.5 s
Nominal lifetime (nom.)	15000 h	Power factor (nom.)	0.5
Switching cycle	50000X	Voltage (Nom)	220-240 V
B50L70	15000 h		
Light Technical		Temperature	
Colour Code	865 [ CCT of 6,500 K]	T ambient (max.)	45 °C
Technical Beam Angle (Nom)	240 °	T ambient (min.)	-20 °C
Lamp Luminous Flux 25°C EL (Nom)	2000 lm	T storage (max.)	65 °C
Lamp Luminous Flux (Nom)	2000 lm	T storage (min.)	-40 °C
Rated beam angle	240 °	T-Case maximum (nom.)	60 °C
Colour Temperature, horizontal (Nom)	6500 K	Controls and Dimming	
Colour consistency	<6	Dimmable	No
Colour Rendering Index, horiz (Nom)	80	Mechanical and Housing	
LLMF at end of nominal lifetime (nom.)	70 %	Product length	1500 mm
Operating and Electrical		Approval and Application	
Input frequency	50 to 60 Hz	Energy efficiency label (EEL)	A+
Power (Rated) (Nom)	20 W	Energy-saving product	Yes
Lamp current (nom.)	155 mA		

# Ecofit Ledtubes T8

Approval marks	CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	20 kWh
<b>Product Data</b>	
Full product code	871869959532600
Order product name	Ecofit LEDtube 1500mm 20W 865 T8
EAN/UPC – product	8718699595326

Order code	59532600
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001338202
Net weight (piece)	0.270 kg



## Dimensional drawing



TLED 5ft 220-240V 20-57W 2000lm 6500K


Product	D1	D2	A1	A2	A3
Ecofit LEDtube 1500mm 20W 865 T8	25.7 mm	28 mm	1500 mm	1507.1 mm	1514.2 mm

## Photometric data



LEDtube Ecofit 16W G13 840 24D ND



LEDtube Ecofit 20W G13 865 24D ND



LEDtube Ecofit 16W G13 865 24D ND



# Ecofit Ledtubes T8

## Lifetime




LEDtube Ecofit 16W G13 840 24D ND

LEDtube Ecofit 16W G13 840 24D ND



LEDtube Ecofit 16W G13 840 24D ND

LEDtube Ecofit 16W G13 840 24D ND



LEDtube Ecofit 16W G13 840 24D ND

## Ecofit Ledtubes T8

