



CorePro LEDtube EM/ Mains T8

CorePro LEDtube 600mm 8W840

Philips CorePro LEDtubes are the quick and easy way to replace T8 fluorescent or other LED tubes with a fast pack back time. Not only does the Core range of LEDtubes require a low initial investment, but LED energy efficiency also delivers instant savings that you can bank on over a long and reliable lifetime. Plus, with the same lamp size and light distribution as fluorescent alternatives, you'll never know the difference. There are two ways to install these LED tubes: Rewire your existing fluorescent-based luminaires so the CorePro LEDtubes work directly on the Mains. Or simply change the fluorescent starter to an LED starter that can be used with your Electromagnetic ballasts.

Warnings and Safety

- NOTE: The overall energy efficiency and light distribution of any installation that uses these lamps will be determined by the design of the installation.
- Installation must be done according to the installation diagrams provided with the lamp or available online. Installation must be done by a certified professional.

Product data


General Information		Luminous Flux	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Luminous Flux	800 lm
Nominal lifetime	30,000 hour(s)	Color Designation	Cool White (CW)
Switching Cycle	200,000	Correlated Color Temperature (Nom)	4000 K
Lighting Technology	LED	Luminous Efficacy (rated) (Nom)	100.00 lm/W
EU RoHS compliant	Yes	Color Consistency	<6
		Color rendering index (CRI)	80
		LLMF At End Of Nominal Lifetime (Nom)	70 %
		Flickering value (PstLM)	2
		Stroboscopic effect value (SVM)	2
Light Technical			
Color Code	840 [CCT of 4000K]		
Beam Angle (Nom)	240 degree(s)		

CorePro LEDtube EM/Mains T8

Photobiological safety according to EN 62471 RGO	
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	8 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V
LED alternative to fluorescent lamp power	18 W
Temperature	
Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Nom)	40 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Material	Glass


Product Length	600 mm
Bulb Shape	T8
Approval and Application	
Energy Saving Product	Yes
Approval Marks	CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	8 kWh
Product Data	
Order product name	CorePro LEDtube 600mm 8W840
Full product name	CorePro LEDtube 600mm 8W840
Full product code	871869671103300
Order code	929001338602
Material Nr. (12NC)	929001338602
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696711033
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696711040

Dimensional drawing



Product	D1	D2	A1	A2	A3
CorePro LEDtube 600mm 8W840	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm

Photometric data




General uniform lighting - CorePro LEDtube 600mm 8W840

Spectral Power Distribution Colour - CorePro LEDtube 600mm 8W840



CorePro LEDtube EM/Mains T8

Photometric data





Light Distribution Diagram - CorePro LEDtube 600mm 8W840

Lifetime



Life Expectancy Diagram - CorePro LEDtube 600mm 8W840

Life Expectancy Diagram - CorePro LEDtube 600mm 8W840




Life Expectancy Diagram - CorePro LEDtube 600mm 8W840

Lumen Maintenance Diagram - CorePro LEDtube 600mm 8W840

CorePro LEDtube EM/Mains T8

Lifetime



Lumen Maintenance Diagram - CorePro LEDtube 600mm 8W840

