



CorePro LEDlinear MV



CorePro LEDlinear ND 7.5-60W R7S 78mm830

CorePro R7S is a retrofit replacement for traditional double-ended linear R7S lamps. Its 'light all around' design delivers light just like a halogen lamp. Within the range you can choose dimmable products which have deep dimming function that enables a cozy ambience when using a dimmable fixture.

Product data

General Information	
Cap-Base	R7s
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
Flux measurement reference	Sphere
CE mark	Yes
EU RoHS compliant	Yes
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	950 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	126.67 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	7.5 W
Lamp Current (Nom)	70 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V

Temperature	
T-Case Maximum (Nom)	104 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Shape	Others


Approval and Application	
Energy Efficiency Class	E
Energy Consumption kWh/1000 h	8 kWh

CorePro LEDlinear MV

EPREL Registration Number	465219
EyeComfort	Yes
Application Conditions	
can it be used in closed luminaires	No
Product Data	
Order product name	CorePro LEDlinear ND 7.5-60W R7S 78mm830
Full product name	CorePro LEDlinear ND 7.5-60W R7S 78mm830


Full product code	871869671394500
Order code	71394500
Material Nr. (12NC)	929001339002
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696713945
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696713952

Dimensional drawing




Product	D	C
CorePro LEDlinear ND 7.5-60W R7S 78mm830	29 mm	78 mm

Photometric data




Spectral Power Distribution Colour - CorePro LEDlinear ND 7.5-60W R7S 78mm830



Accent Lighting Spots - CorePro LEDlinear ND 7.5-60W R7S 78mm830


CorePro LEDlinear MV

Photometric data




Light Distribution Diagram - CorePro LEDlinear ND 7.5-60W R7S 78mm830

Lifetime



Life Expectancy Diagram - CorePro LEDlinear ND 7.5-60W R7S 78mm830



Lumen Maintenance Diagram - CorePro LEDlinear ND 7.5-60W R7S 78mm830

