

CorePro LEDlinear MV



CorePro LEDlinear ND 7.5-60W R7S 78mm830

CorePro R7S is a retrofit replacement for traditional double-ended linear R7S lamps. Its 'light all around' design delivers light that is just like a halogen lamp. Within the range, you can choose dimmable products which have deep a dimming function that enables a cosy ambience when using a dimmable fixture.

Product data


General Information		Input frequency	
Cap base	R7s	Input frequency	50 to 60 Hz
Nominal lifetime	15,000 h	Power Consumption	7.5 W
Switching Cycle	50,000	Lamp current (nom.)	70 mA
Lighting Technology	LED	Wattage equivalent	60 W
Flux measurement reference	Sphere	Starting time (nom.)	0.5 s
CE mark	Yes	Warm-up time to 60% light	0.5 s
EU RoHS compliant	Yes	Power Factor (Fraction)	0.5
		Voltage (nom.)	220-240 V
Light Technical		Temperature	
Colour Code	830 [CCT of 3000K]	T-Case maximum (nom.)	104 °C
Luminous Flux	950 lm		
Colour designation	White (WH)	Controls and Dimming	
Correlated Colour Temperature	3000 K	Dimmable	No
Luminous efficacy (rated) (nom.)	126.67 lm/W		
Colour consistency	<6	Mechanical and Housing	
Colour rendering index (CRI)	80	Bulb shape	Others
LLMF at end of nominal lifetime (nom.)	70 %		
Flickering value (PstLM)	1	Approval and Application	
Stroboscopic effect	0.4	Energy Efficiency Class	E
		Energy consumption kWh/1,000 hours	8 kWh
		EPREL registration number	465219
Operating and Electrical			
Line Frequency	50 to 60 Hz		

CorePro LEDlinear MV

EyeComfort	Yes
Application Conditions	
Can it be used in closed luminaires	No
Product Data	
Order product name	CorePro LEDlinear ND 7.5-60W R7S 78mm830
Full product name	CorePro LEDlinear ND 7.5-60W R7S 78mm830
Full EOC	871869671394500



Order code	71394500
Material no. (12 NC)	929001339002
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696713945
Numerator – packs per outer box	10
EAN/UPC - Case	8718696713952

Dimensional drawing




Product	D	C
CorePro LEDlinear ND 7.5-60W R7S 78mm830	29 mm	78 mm

Photometric data



Spectral Power Distribution Colour - CorePro LEDlinear ND 7.5-60W R7S 78mm830



Accent Lighting Spots - CorePro LEDlinear ND 7.5-60W R7S 78mm830



Light Distribution Diagram - CorePro LEDlinear ND 7.5-60W R7S 78mm830

CorePro LEDlinear MV

Lifetime



Life Expectancy Diagram - CorePro LEDlinear ND 7.5-60W R7S 78mm830

Lumen Maintenance Diagram - CorePro LEDlinear ND 7.5-60W R7S 78mm830

