



LED PAR30 S/L

12PAR30S/EXPERTCOLOR/F25/940/DIM

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	40,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	940 [CCT of 4000K]
Beam Angle (Nom)	25 degree(s)
Luminous Flux	950 lm
Luminous Intensity (Nom)	4,800 cd
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	75.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	95
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	12 W
Lamp Current (Nom)	120 mA


Wattage Equivalent	75 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	90 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Plastic
Bulb Shape	PAR30S
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh
Energy Certifications	Energy Star
Product Data	
Order product name	12PAR30S/EXPERTCOLOR/F25/940/DIM

LED PAR30 S/L

Full product name	12PAR30S/EXPERTCOLOR/F25/940/DIM
Order code	470930
Material Nr. (12NC)	929001340704
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677470937


Numerator - Packs per outer box	6
EAN/UPC - Case	50046677470932

Dimensional drawing




Product	D	C
12PAR30S/EXPERTCOLOR/F25/940/DIM	120.7 mm	134.6 mm


Photometric data



Spectral Power Distribution Colour - 12PAR30S/EXPERTCOLOR/F25/940/DIM




Accent Lighting Spots - 12PAR30S/EXPERTCOLOR/F25/940/DIM




Light Distribution Diagram - 12PAR30S/EXPERTCOLOR/F25/940/DIM

LED PAR30 S/L

Lifetime



Life Expectancy Diagram - 12PAR30S/EXPERTCOLOR/F25/940/DIM



Lumen Maintenance Diagram - 12PAR30S/EXPERTCOLOR/F25/940/DIM

