



MASTER LEDspot ExpertColor LV

MAS LED MR16 ExpertColor 7.2-50W 927 60D

MASTER LEDspot LV ExpertColor 能為接待區、居家和餐廳營造溫暖舒適的氣氛。這款產品具備出色的照明品質，提供自訂的色彩光譜選擇，高流明 (CRI) 和深度調光特色，當然是營造唯美燈光照明的頂尖高手。不僅如此，這款產品的創新、無痕美學燈泡設計，外型簡約時尚，適合幾乎各種室內裝潢。此外，這款產品也是 ExpertColor 系列產品，同系列產品還包括 LEDspot MV 和 LEDspot Par 燈泡。

产品数据

一般資訊	
燈座基底	GU5.3 [GU5.3]
標稱使用壽命	40,000 h
切換週期	50,000
照明技術	LED
符合歐盟 RoHS 標準	是
照明技術	
色碼	927
光束角 (Nom)	60 °
光通量	450 lm
光強 (標稱)	410 cd
色彩名稱	暖白光 (WW)
相關色彩溫度 (規範)	2700 K
光效 (額定) (標準)	62.50 lm/W
色彩一致性	<3
演色性指數 (CRI)	97
LLMF 標稱壽命結束 (規範)	70 %


運轉與電力	
線路頻率	- Hz
輸入頻率	- Hz
耗電量	7.2 W
燈具電流 (標稱)	800 mA
相等瓦數	50 W
起始時間 (標稱)	0.5 s
達到 60% 光色的熱穩時間	1 s
功率因數 (比值)	0.7
電壓 (標稱)	12 V
溫度	
T 盒上限 (正常情況)	92 °C
控制與調光	
可調光	是
機械與外罩	
燈泡形狀	MR16 [2 吋/50mm]

MASTER LEDspot ExpertColor LV

認證與應用	
適合補強燈	是
能源消耗 kWh/1000 h	- kWh
產品資料	
下訂產品名稱	MAS LED MR16 ExpertColor 7.2-50W 927 60D
完整產品名稱	MAS LED MR16 ExpertColor 7.2-50W 927 60D
完整產品代碼	871869671950300


訂單代碼	929001341408
材質 Nr. (12NC)	929001341408
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8718696719503
分子 - 每一外盒包裝	10
EAN/UPC - 箱	8718696719510

二维绘图




Product	D	C
MAS LED MR16 ExpertColor 7.2-50W 927 60D	50.5 mm	46 mm

光度数据



**Spectral Power Distribution Colour - MAS LED MR16 ExpertColor 7.2-50W
927 60D**




Accent Lighting Spots - MAS LED MR16 ExpertColor 7.2-50W 927 60D




Light Distribution Diagram - MAS LED MR16 ExpertColor 7.2-50W 927 60D

MASTER LEDspot ExpertColor LV

壽命



Life Expectancy Diagram - MAS LED MR16 ExpertColor 7.2-50W 927 60D



Lumen Maintenance Diagram - MAS LED MR16 ExpertColor 7.2-50W 927 60D

