

MASTER LED ExpertColor LED MR16 ExpertColor 7.2-50W 930 60D
MASTER LEDspot ExpertColor LV



MASTER LEDspot LV ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. It creates such an ambience with superior lighting that has a customised spectrum, high CRI and deep dimming feature. The result? A beautiful lighting experience. What's more, the innovative, trimless lens design will suit almost any interior decor with its clean and neat look. In addition, you can take advantage of the full ExpertColor family, which also includes LEDspot MV and LEDspot Par lamps.

Our Eco passport



Energy

- **Dimmable:** Yes
- **Energy efficiency label (EEL):** Not applicable
- **Luminous efficacy (rated) (nom.):** 66.67 lm/W
- **Power (Rated) (Nom):** 7.2 W



Circularity

- **Nominal lifetime (nom.):** 40000 h



Packaging

- **SAP Weight Paper Unit (Case):** 0.140 kg
- **SAP Weight Paper Unit (Piece):** 0.008 kg



Substances

- **EU RoHS compliant:** No



Weight & Materials

- **Net weight (piece):** 0.034 kg

Energy efficiency ranking / External awards

