

**PHILIPS**

Eco passport

## MASTER LED ExpertColor LED MR16 ExpertColor 7.2-50W 930 60D MASTER LEDspot ExpertColor LV

MASTER LEDspot LV ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. It creates such an ambience with superior lighting that has a customised spectrum, high CRI and deep dimming feature. The result? A beautiful lighting experience. What's more, the innovative, trimless lens design will suit almost any interior decor with its clean and neat look. In addition, you can take advantage of the full ExpertColor family, which also includes LEDspot MV and LEDspot Par lamps.



### Our Eco passport



#### Energy

- **Dimmable:** Yes
- **Energy efficiency label (EEL):** Not applicable
- **Lamp Luminous Efficacy EM (Nom):** 66.67 lm/W
- **Power (Rated) (Nom):** 7.2 W



#### Circularity

- **Nominal lifetime (nom.):** 40000 h



#### Packaging

- **SAP Weight Paper Unit (Case):** 0.140 kg
- **SAP Weight Paper Unit (Piece):** 0.008 kg



#### Substances

- **EU RoHS compliant:** No



#### Weight & Materials

- **Net weight (piece):** 0.034 kg

#### Energy efficiency ranking / External awards

