



# MASTER LEDspot PAR

## MAS LEDspot CLA D 9.5-75W 830 PAR30S 25D

With its robust design and warm-white beam of light, these new-generation PAR lamps are ideal for general lighting and spot lighting in the hospitality industry. There is a choice of dimmable and non-dimmable versions. They are especially suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 holder and designed for retrofit replacement of halogen/incandescent lamps, MASTER LEDspot PAR deliver huge energy savings and minimize maintenance cost without any reduction in brightness. The IP44-rated outdoor version of the PAR 38 lamp is one of the few energy-saving alternatives to incandescent PAR38 outdoor lamps available today. The dimmable PAR 20 is a perfect replacement for an incandescent spot.

### Product data

| General Information                  |                       |
|--------------------------------------|-----------------------|
| Cap base                             | E27 [ E27]            |
| Nominal lifetime (nom.)              | 25000 h               |
| Technical type                       | 9.5-75W               |
| Light Technical                      |                       |
| Colour code                          | 830 [ CCT of 3,000 K] |
| Beam Angle (Nom)                     | 25 °                  |
| Luminous flux (nom.)                 | 760 lm                |
| Luminous flux (rated) (nom.)         | 760 lm                |
| Luminous intensity (nom.)            | 3500 cd               |
| Colour designation                   | White (WH)            |
| Rated beam angle                     | 25 °                  |
| Correlated colour temperature (nom.) | 3000 K                |
| Luminous efficacy (rated) (nom.)     | 85.26 lm/W            |
| Colour consistency                   | <6                    |
| Color rendering index (nom.)         | 80                    |

| LLMF at end of nominal lifetime (nom.) | 70 %      |
|--|-----------|
| Luminous Flux in 90° Cone (Rated)      | 760 lm    |
| Operating and Electrical               |           |
| Input frequency                        | 50 Hz     |
| Power (Rated) (Nom)                    | 9.5 W     |
| Lamp current (nom.)                    | 48 mA     |
| Wattage equivalent                     | 75 W      |
| Starting time (nom.)                   | 0.5 s     |
| Warm-up time to 60% light (nom.)       | 0.5 s     |
| Power factor (nom.)                    | 0.85      |
| Voltage (Nom)                          | 220-240 V |
| Controls and Dimming                   |           |
| Dimmable                               | Yes       |

# MASTER LEDspot PAR

## Approval and Application


|                               |        |
|-------------------------------|--------|
| Energy efficiency label (EEL) | A+     |
| Suitable for accent lighting  | Yes    |
| Energy Consumption kWh/1000 h | 10 kWh |

## Product Data

|                    |  |
|--------------------|--|
| Full product code  | 871869671390700                          |
| Order product name | MAS LEDspot CLA D 9.5-75W 830 PAR30S 25D |

|                                 |               |
|---------------------------------|---------------|
| EAN/UPC – product               | 8718696713907 |
| Order code                      | 71390700      |
| Numerator – quantity per pack   | 1             |
| Numerator – packs per outer box | 6             |
| Material no. (12NC)             | 929001342902  |
| Net weight (piece)              | 0.230 kg      |


## Dimensional drawing




PAR30s 220-240V 9-75W 800lm 3000K E27 D

| Product                                  | D     | C     |
|--|-------|-------|
| MAS LEDspot CLA D 9.5-75W 830 PAR30S 25D | 95 mm | 86 mm |

## Photometric data




© 2019 Philips Lighting B.V.



MASTER LEDspot PAR 75W E27 830 25D


MASTER LEDspot PAR 75W E27 830 25D



MASTER LEDspot PAR 75W E27 830 25D

# MASTER LEDspot PAR

## Lifetime



MASTER LEDspot PAR 50W E27 827 25D

MASTER LEDspot PAR 50W E27 827 25D

