

CorePro LEDtube InstantFit T8

14T8/PRO/48-830/IF20/G 10/1 FB

The CorePro LED Type A - Ballast Driven (Plug and Play) InstantFit TLED is a great LED solutionsuitable for replacing T8 fluorescent lamps, using an existing ballast. Specific lamps can also be used on Philips Xitanium driver for Type C applications.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Main Application	Indoor
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X
B50L70	50000 h

Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux (Nom)	2000 lm
Luminous Flux (Rated) (Nom)	2000 lm
Correlated Color Temperature (Nom)	3000 K
Color Consistency	<6
Color Rendering Index (Nom)	82
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	25000-105000 Hz
Power (Rated) (Nom)	14 W
Lamp Current (Max)	260 mA
Lamp Current (Min)	100 mA

Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	120-277, 347 V

Temperature	
T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C
T-Case Maximum (Nom)	50 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Product Length	1200 mm

Approval and Application	
Energy Efficiency Label (EEL)	Not applicable
Energy Saving Product	Yes

CorePro LEDtube InstantFit T8


Approval Marks	UL certificate RoHS compliance DLC compliance
DesignLights Consortium Qualified Product List	DesignLights Consortium Qualified Product List

Product Data

Order product name	14T8/PRO/48-830/IF20/G 10/1 FB
EAN/UPC - Product	046677452407

Order code	929001343034
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001343034
Net Weight (Piece)	0.215 kg


Dimensional drawing




14T8 PRO LED/48-3000 IF G 10/1

Product	D1	D2	A1	A2	A3
14T8/PRO/48-830/IF20/G 10/1 FB	25.7 mm	28 mm	1198 mm	1205 mm	1212 mm


Photometric data



LEDtube 1200mm 17W G13 2100lm





LEDtube PRO 1200mm 14W G13 830 2000lm



LEDtube PRO 1200mm 14W G13 830 2000lm



CorePro LEDtube InstantFit T8

Lifetime




LEDtube PRO 1200mm 14W G13 2000lm

LEDtube PRO 1200mm 14W G13 2000lm



12W G13

12W G13



12W G13

CorePro LEDtube InstantFit T8

