



Classic frosted LED candles and lustres



Classic LEDCandle ND 2.2-25W B35 E14 FR

Featuring a classic heritage design, Classic frosted LED candles and lustres deliver beautiful, decorative warm-white light while saving around 90% on energy costs. The familiar shapes of Classic frosted LED candles and lustres are a perfect fit for your existing fixtures.

Product data


General Information	
Cap base	E14 [E14]
Nominal lifetime	15,000 h
Switching Cycle	20,000
Lighting Technology	LED
Flux measurement reference	Sphere
EU RoHS compliant	Yes
Light Technical	
Colour Code	827 [CCT of 2700K]
Luminous Flux	250 lm
Colour designation	Warm White (WW)
Correlated Colour Temperature	2700 K
Luminous efficacy (rated) (nom.)	113.00 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz

Input frequency	50 to 60 Hz
Power Consumption	2.2 W
Lamp current (nom.)	21 mA
Wattage equivalent	25 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.4
Voltage (nom.)	220-240 V
Temperature	
T-Case maximum (nom.)	36 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Lamp Finish	Frosted
Bulb shape	B35 [B 35 mm]


Classic frosted LED candles and lustres

Approval and Application	
Energy Efficiency Class	E
Energy consumption kWh/1,000 hours	3 kWh
EPREL registration number	387381
EyeComfort	Yes
Product Data	
Order product name	CLA LEDCandle ND 2.2-25W B35 E14 FR
Full product name	Classic LEDCandle ND 2.2-25W B35 E14 FR

Dimensional drawing




Photometric data




Spectral Power Distribution Colour - CLA LEDCandle ND 2.2-25W B35 E14 FR

Full EOC	871869670637400
Order code	70637400
Material no. (12 NC)	929001345202
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696706374
Numerator – packs per outer box	10
EAN/UPC - Case	8718696706381

Product	D	C
CLA LEDCandle ND 2.2-25W B35 E14 FR	35 mm	97 mm




General uniform lighting - CLA LEDCandle ND 2.2-25W B35 E14 FR




Light Distribution Diagram - CLA LEDCandle ND 2.2-25W B35 E14 FR

Classic frosted LED candles and lustres

Lifetime



Life Expectancy Diagram - CLA LEDCandle ND 2.2-25W B35 E14 FR



Lumen Maintenance Diagram - CLA LEDCandle ND 2.2-25W B35 E14 FR

