



Classic frosted LED candles and lusters



CLA LEDCandle ND 4.3-40W E14 827 B35 FR

Featuring a classic heritage design, Classic forsted LED candles and lusters deliver beautiful, decorative warm-white light while saving around 90% on energy costs. The familiar shapes of Classic forsted LED candles and lusters are a perfect fit for your existing fixtures.

Product data


General Information	
Cap-Base	E14 [E14]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
Flux measurement reference	Sphere
EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	470 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	109.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz

Input Frequency	50 to 60 Hz
Power Consumption	4.3 W
Lamp Current (Nom)	35 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	55 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	B35 [B 35mm]

Classic frosted LED candles and lusters

Approval and Application	
Energy Efficiency Class	F
Energy Consumption kWh/1000 h	5 kWh
EPREL Registration Number	387382
EyeComfort	Yes
Product Data	
Order product name	CLA LEDCandle ND 4.3-40W E14 827 B35 FR
Full product name	CLA LEDCandle ND 4.3-40W E14 827 B35 FR


Dimensional drawing




Full product code	871869670639800
Order code	929001345302
Material Nr. (12NC)	929001345302
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696706398
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696706404

Product	D	C
CLA LEDCandle ND 4.3-40W E14 827 B35 FR	35 mm	97 mm


Photometric data



Spectral Power Distribution Colour - CLA LEDCandle ND 4.3-40W E14 827 B35 FR




General uniform lighting - CLA LEDCandle ND 4.3-40W E14 827 B35 FR




Light Distribution Diagram - CLA LEDCandle ND 4.3-40W E14 827 B35 FR

Classic frosted LED candles and lusters

Lifetime



Life Expectancy Diagram - CLA LEDCandle ND 4.3-40W E14 827 B35 FR



Lumen Maintenance Diagram - CLA LEDCandle ND 4.3-40W E14 827 B35 FR

