



# Classic frosted LED candles and lusters

## CLA LEDLuster ND 4.3-40W E27 827 P45 FR

Featuring a classic heritage design, Classic frosted LED candles and lusters deliver beautiful, decorative warm-white light while saving around 90% on energy costs. The familiar shapes of Classic frosted LED candles and lusters are a perfect fit for your existing fixtures.

### Product data

| General Information                   |                    |
|---------------------------------------|--------------------|
| Cap-Base                              | E27 [E27]          |
| Nominal lifetime                      | 15,000 hour(s)     |
| Switching Cycle                       | 20,000             |
| Lighting Technology                   | LED                |
| Flux measurement reference            | Sphere             |
| EU RoHS compliant                     | Yes                |
| Light Technical                       |                    |
| Color Code                            | 827 [CCT of 2700K] |
| Luminous Flux                         | 470 lm             |
| Color Designation                     | Warm White (WW)    |
| Correlated Color Temperature (Nom)    | 2700 K             |
| Luminous Efficacy (rated) (Nom)       | 109.00 lm/W        |
| Color Consistency                     | <6                 |
| Color rendering index (CRI)           | 80                 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 %               |
| Operating and Electrical              |                    |
| Line Frequency                        | 50 to 60 Hz        |

| Input Frequency           | 50 to 60 Hz  |
|---------------------------|--------------|
| Power Consumption         | 4.3 W        |
| Lamp Current (Nom)        | 35 mA        |
| Wattage Equivalent        | 40 W         |
| Starting Time (Nom)       | 0.5 s        |
| Warm-up time to 60% light | 0.5 s        |
| Power Factor (Fraction)   | 0.5          |
| Voltage (Nom)             | 220-240 V    |
| Temperature               |              |
| T-Case Maximum (Nom)      | 55 °C        |
| Controls and Dimming      |              |
| Dimmable                  | No           |
| Mechanical and Housing    |              |
| Bulb Finish               | Frosted      |
| Bulb Shape                | P45 [P 45mm] |

Classic frosted LED candles and lusters


|                               |                                         |
|-------------------------------|-----------------------------------------|
| Approval and Application      |                                         |
| Energy Efficiency Class       | F                                       |
| Energy Consumption kWh/1000 h | 5 kWh                                   |
| EPREL Registration Number     | 387386                                  |
| EyeComfort                    | Yes                                     |
| Product Data                  |                                         |
| Order product name            | CLA LEDLuster ND 4.3-40W E27 827 P45 FR |
| Full product name             | CLA LEDLuster ND 4.3-40W E27 827 P45 FR |

Dimensional drawing


|                                 |                 |
|---------------------------------|-----------------|
| Full product code               | 871869670647300 |
| Order code                      | 929001345702    |
| Material Nr. (12NC)             | 929001345702    |
| Numerator - Quantity Per Pack   | 1               |
| EAN/UPC - Product/Case          | 8718696706473   |
| Numerator - Packs per outer box | 10              |
| EAN/UPC - Case                  | 8718696706480   |

| Product                                 | D     | C     |
|-----------------------------------------|-------|-------|
| CLA LEDLuster ND 4.3-40W E27 827 P45 FR | 45 mm | 78 mm |

Photometric data



Spectral Power Distribution Colour - CLA LEDLuster ND 4.3-40W E27 827 P45 FR




General uniform lighting - CLA LEDLuster ND 4.3-40W E27 827 P45 FR


Light Distribution Diagram - CLA LEDLuster ND 4.3-40W E27 827 P45 FR

Classic frosted LED candles and lusters

Lifetime



Life Expectancy Diagram - CLA LEDLuster ND 4.3-40W E27 827 P45 FR



Lumen Maintenance Diagram - CLA LEDLuster ND 4.3-40W E27 827 P45 FR

