



MASTER LEDtube InstantFit HF T5

MAS LEDtube HF 1500mm UO 36W 865 T5

Philips MASTER LEDtube InstantFit T5 integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescents. The Philips MASTER LEDtube InstantFit T5 is the ideal solution for customers who have higher light output requirements and want to maximise value over the lifetime. The full energy savings & longer lifetime result in attractive payback times and TCO benefits.

Product data

General Information	
Cap base	G5 [G5]
Nominal lifetime (nom.)	50000 h
Switching cycle	50000X
B50L70	50000 h

Light Technical	
Colour Code	865 [CCT of 6500K]
Lamp Luminous Flux 25°C EL (Nom)	5600 lm
Lamp Luminous Flux (Nom)	5600 lm
Colour Temperature, horizontal (Nom)	6500 K
Colour consistency	<6
Colour Rendering Index,horiz (Nom)	83
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Technical Lamp Power (Nom)	36 W
Lamp current (max.)	750 mA
Lamp current (min.)	550 mA

Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Voltage (nom.)	65-75 V

Temperature	
T ambient (max.)	45 °C
T ambient (min.)	-20 °C
T storage (max.)	65 °C
T storage (min.)	-40 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Product length	1500 mm


Approval and Application	
Energy-saving product	Yes
Energy efficiency label (EEL)	A++

MASTER LEDtube InstantFit HF T5

Approval marks	CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	42 kWh
Product Data	
Full product code	871869670605300
Order product name	MAS LEDtube HF 1500mm UO 36W 865 T5
EAN/UPC – product	8718696706053

Order code	929001346302
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001346302
Net weight (piece)	0.170 kg




Dimensional drawing



TLED 230V 37-80W 5600lm 160D 6500K G5 ND





Product	D1	D2	A1	A2	A3
MAS LEDtube HF 1500mm UO 36W 865 T5	15.2 mm	21 mm	1447.8 mm	1454.9 mm	1462 mm

Photometric data




MASTER LEDtube InstantFit HF T5

Lifetime



LEDtube 1500mm 36W G5 5600lm

LEDtube 1200mm 26W G5 3900lm



LEDtube 1500mm 36W G5 5600lm

