



MASTER LEDspot ExpertColor MV

MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 36D

MASTER LEDspot MV ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. It creates ambience with superior lighting that has a customised spectrum, high CRI and deep dimming features. The result? A beautiful lighting experience. What's more, the innovative, trimless lens design will also suit almost any interior decor with its clean and neat look.

Product data

General Information	
Cap base	GU10 [GU10]
Nominal lifetime (nom.)	40000 h
Switching cycle	50000X
Technical type	5.5-50W
Light Technical	
Colour Code	927
Technical Beam Angle (Nom)	36 °
Lamp Luminous Flux 25°C EL (Nom)	385 lm
Lamp Luminous Flux (Nom)	385 lm
Luminous intensity (nom.)	800 cd
Colour Designation	Warm white (WW)
Rated beam angle	36 °
Colour Temperature, horizontal (Nom)	2700 K
Lamp Luminous Efficacy EM (Nom)	70.00 lm/W
Colour consistency	<3
Colour Rendering Index,horiz (Nom)	97

LLMF at end of nominal lifetime (nom.)	70 %
Luminous Flux in 90° Cone (Rated)	355 lm
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	5.5 W
Lamp current (nom.)	30 mA
Wattage equivalent	50 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.8
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	80 °C

MASTER LEDspot ExpertColor MV

Controls and Dimming

Dimmable	Yes
----------	-----

Approval and Application


Energy efficiency label (EEL)	A+
Suitable for accent lighting	Yes
Energy Consumption kWh/1000 h	6 kWh

Product Data

Full product code	871869670733300
Order product name	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 36D

EAN/UPC – product	8718696707333
Order code	929001347308
Local Code	MEC405L36D927GU
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001347308
Net weight (piece)	0.038 kg


Dimensional drawing




GU10 230V5.5W-50W345lm40D 2700K GU10 Dim

Product	D	C
MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 36D	50 mm	54 mm

Photometric data




MASTER LEDspot ExpertColor MV 50W GU10 927 36D



MASTER LEDspot ExpertColor MV 50W GU10 927 36D

MASTER LEDspot ExpertColor MV

Photometric data



MASTER LEDspot ExpertColor MV 50W GU10 927 36D

Lifetime



MASTER LEDspot ExpertColor MV 35W GU10 25D



MASTER LEDspot ExpertColor MV 35W GU10 25D

