



MASTER LEDspot MV

Master LED 5-50W GU10 927 36D Dim

Delivering a warm, halogen-like accent beam, MASTER LEDspot MV is a perfect fit for spot lighting (track, corridors, lift lobbies, display cases and cabinets) in the hospitality industry. It is particularly suitable to public areas where the light is on 24/7, such as lobbies, corridors, stairwells. MASTER LEDspot MV delivers huge energy savings and minimizes maintenance cost without any compromise on brightness, enabling hospitality owners to achieve a return on their investment within one year. These LEDspots are compatible with most existing fixtures with a GU10 holder and designed as a retrofit replacement for halogen or incandescent spots. The dimmable versions drive further efficiencies, while helping to create the desired atmosphere.

Product data

General Information	
Cap base	GU10 [GU10]
Nominal lifetime (nom.)	25000 h
Switching cycle	50000X
Technical type	5-50W
Light Technical	
Colour code	927
Beam Angle (Nom)	36 °
Luminous flux (nom.)	395 lm
Luminous flux (rated) (nom.)	395 lm
Luminous intensity (nom.)	650 cd
Colour designation	Warm White (WW)
Rated beam angle	36 °
Correlated colour temperature (nom.)	2700 K
Luminous efficacy (rated) (nom.)	80.61 lm/W
Colour consistency	<6

Color rendering index (nom.)	90
LLMF at end of nominal lifetime (nom.)	70 %
Luminous Flux in 90° Cone (Rated)	355 lm
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	5 W
Lamp current (nom.)	27 mA
Wattage equivalent	50 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.8
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	80 °C

MASTER LEDspot MV

Controls and Dimming

Dimmable Yes

Approval and Application

Energy efficiency label (EEL) A+
 Suitable for accent lighting Yes
 Energy Consumption kWh/1000 h 5 kWh

Product Data


Full product code 871869670731900

Order product name	Master LED 5-50W GU10 927 36D Dim
EAN/UPC – product	8718696707319
Order code	70731900
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001348808
Net weight (piece)	0.038 kg

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights


Dimensional drawing




GU10 230V5W-50W 345lm 36D 2700K GU10 Dim

Product	D	C
Master LED 5-50W GU10 927 36D Dim	50 mm	54 mm

Photometric data




MASTER LEDspotMV 50W GU10 927 36D 355lm



MASTER LEDspotMV 35W GU10 927 36D 260lm


MASTER LEDspot MV

Photometric data




MASTER LEDspotMV 50W GU10 36D 355lm

Lifetime



MASTER LEDspotMV GU10 922-927 36D



MASTER LEDspotMV GU10 922-927 36D

