



MASTER VALUE LEDspot MV

Master LED 4.9-50W GU10 927 36D Dim

Delivering a warm, halogen-like accent beam, MASTER VALUE is a perfect fit for spot lighting. Thanks to its high CRI, it realizes more natural colors, creating cozy and comfortable ambiances for residential and hospitality projects, and emphasizing the beauty of merchandise in retail. These LED spots MV GU10 have the familiar look and feel of spot lamps, keeping the classic beauty of glass spots and adding the strong performance of LED technology. The dimming function enables you to create the atmosphere you desire, and it works with broad selection of dimmers. MASTER VALUE also offers more energy savings than normal LED spots.

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

Product data

General Information			
Cap-Base	GU10	Luminous Intensity (Nom)	650 cd
Nominal lifetime	25,000 hour(s)	Color Designation	Warm White (WW)
Switching Cycle	50,000	Correlated Color Temperature (Nom)	2700 K
Lighting Technology	LED	Luminous Efficacy (rated) (Nom)	80.61 lm/W
EU RoHS compliant	Yes	Color Consistency	<6
		Color rendering index (CRI)	90
		LLMF At End Of Nominal Lifetime (Nom)	70 %
		Luminous Flux in 90° Cone (Rated)	355 lm
Light Technical		Operating and Electrical	
Color Code	927	Line Frequency	50 to 60 Hz
Beam Angle (Nom)	36 degree(s)		
Luminous Flux	395 lm		

MASTER VALUE LEDspot MV

Input Frequency	50 to 60 Hz
Power Consumption	5 W
Lamp Current (Nom)	27 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.8
Voltage (Nom)	220-240 V

Temperature

T-Case Maximum (Nom)	80 °C
----------------------	-------

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Bulb Shape	PAR16
------------	-------

Approval and Application

Suitable For Accent Lighting	Yes
------------------------------	-----

Energy Consumption kWh/1000 h	5 kWh
EyeComfort	Yes


Application Conditions

can it be used in closed luminaires	No
-------------------------------------	----

Product Data

Order product name	Master LED 4.9-50W GU10 927 36D Dim
Full product name	Master LED 4.9-50W GU10 927 36D Dim
Full product code	871869670731900
Order code	929001348808
Material Nr. (12NC)	929001348808
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696707319
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696707326

Dimensional drawing



Product	D	C
Master LED 4.9-50W GU10 927 36D Dim	50 mm	54 mm

Photometric data





Diagram of Photometric Data - Master LED 4.9-50W GU10 927 36D Dim




Spectral Power Distribution Colour - Master LED 4.9-50W GU10 927 36D Dim

Accent Lighting Spots - Master LED 4.9-50W GU10 927 36D Dim


MASTER VALUE LEDspot MV

Photometric data




Light Distribution Diagram - Master LED 4.9-50W GU10 927 36D Dim

Lifetime



Life Expectancy Diagram - Master LED 4.9-50W GU10 927 36D Dim



Lumen Maintenance Diagram - Master LED 4.9-50W GU10 927 36D Dim

