



MASTER VALUE LEDspot MV

Master LED 4.9-50W GU10 927 36D Dim

Delivering a warm, halogen-like accent beam, MASTER VALUE is a perfect fit for spot lighting. Thanks to its high CRI, it realizes more natural colors, creating cozy and comfortable ambiances for residential and hospitality projects, and emphasizing the beauty of merchandise in retail. These LED spots MV GU10 have the familiar look and feel of spot lamps, keeping the classic beauty of glass spots and adding the strong performance of LED technology. The dimming function enables you to create the atmosphere you desire, and it works with broad selection of dimmers. MASTER VALUE also offers more energy savings than normal LED spots.

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

Product data

| General Information | |
|---------------------|----------------|
| Cap-Base | GU10 |
| Nominal lifetime | 25,000 hour(s) |
| Switching Cycle | 50,000 |
| Lighting Technology | LED |
| EU RoHS compliant | Yes |
| Light Technical | |
| Color Code | 927 |
| Beam Angle (Nom) | 36 degree(s) |
| Luminous Flux | 395 lm |

| | |
|---------------------------------------|-----------------|
| Luminous Intensity (Nom) | 650 cd |
| Color Designation | Warm White (WW) |
| Correlated Color Temperature (Nom) | 2700 K |
| Luminous Efficacy (rated) (Nom) | 80.61 lm/W |
| Color Consistency | <6 |
| Color rendering index (CRI) | 90 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |
| Luminous Flux in 90° Cone (Rated) | 355 lm |

| Operating and Electrical | |
|--------------------------|-------------|
| Line Frequency | 50 to 60 Hz |

MASTER VALUE LEDspot MV

| | |
|---------------------------|-------------|
| Input Frequency | 50 to 60 Hz |
| Power Consumption | 5 W |
| Lamp Current (Nom) | 27 mA |
| Wattage Equivalent | 50 W |
| Starting Time (Nom) | 0.5 s |
| Warm-up time to 60% light | 0.5 s |
| Power Factor (Fraction) | 0.8 |
| Voltage (Nom) | 220-240 V |

Temperature

| | |
|----------------------|-------|
| T-Case Maximum (Nom) | 80 °C |
|----------------------|-------|

Controls and Dimming

| | |
|----------|-----|
| Dimmable | Yes |
|----------|-----|

Mechanical and Housing

| | |
|------------|-------|
| Bulb Shape | PAR16 |
|------------|-------|

Approval and Application

| | |
|------------------------------|-----|
| Suitable For Accent Lighting | Yes |
|------------------------------|-----|

| | |
|-------------------------------|-------|
| Energy Consumption kWh/1000 h | 5 kWh |
| EyeComfort | Yes |


Application Conditions

| | |
|-------------------------------------|----|
| can it be used in closed luminaires | No |
|-------------------------------------|----|

Product Data



| | |
|---------------------------------|-------------------------------------|
| Order product name | Master LED 4.9-50W GU10 927 36D Dim |
| Full product name | Master LED 4.9-50W GU10 927 36D Dim |
| Full product code | 871869670731900 |
| Order code | 929001348808 |
| Material Nr. (12NC) | 929001348808 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8718696707319 |
| Numerator - Packs per outer box | 10 |
| EAN/UPC - Case | 8718696707326 |

Dimensional drawing



| Product | D | C |
|-------------------------------------|-------|-------|
| Master LED 4.9-50W GU10 927 36D Dim | 50 mm | 54 mm |

Photometric data




Accent Lighting Spots - Master LED 4.9-50W GU10 927 36D Dim

Spectral Power Distribution Colour - Master LED 4.9-50W GU10 927 36D Dim

MASTER VALUE LEDspot MV

Photometric data



Light Distribution Diagram - Master LED 4.9-50W GU10 927 36D Dim

Lifetime



Life Expectancy Diagram - Master LED 4.9-50W GU10 927 36D Dim



Lumen Maintenance Diagram - Master LED 4.9-50W GU10 927 36D Dim

