



# MASTER VALUE LEDspot MV

## Master LED 4.9-50W GU10 927 36D Dim

Delivering a warm, halogen-like accent beam, MASTER VALUE LEDspot MV is a perfect for spot lighting. Thanks to its high CRI, it realizes more natural colors, enabling cozy and comfortable ambience for residential, hospitality and emphasize the beauty of merchandise in retail. These LEDspots have the familiar look and feel of glass spots, keeping the classic beauty of glass spots and adding the strong performance from LED technology. The dimming function enables to create the desired atmosphere and it works with broad selection of dimmers.

### Product data

General Information		Luminous Flux in 90° Cone (Rated)	
Cap-Base	GU10 [ GU10]		355 lm
EU RoHS compliant	Yes	Operating and Electrical	
Nominal Lifetime (Nom)	25000 h	Input Frequency	50 to 60 Hz
Switching Cycle	50000X	Power (Nom)	5 W
Technical Type	5-50W	Lamp Current (Nom)	27 mA
Light Technical		Wattage Equivalent	50 W
Color Code	927	Starting Time (Nom)	0.5 s
Beam Angle (Nom)	36 °	Warm Up Time to 60% Light (Nom)	0.5 s
Luminous Flux (Nom)	395 lm	Power Factor (Nom)	0.8
Luminous Intensity (Nom)	650 cd	Voltage (Nom)	220-240 V
Color Designation	Warm White (WW)	Temperature	
Correlated Color Temperature (Nom)	2700 K	T-Case Maximum (Nom)	80 °C
Luminous Efficacy (rated) (Nom)	80.61 lm/W	Controls and Dimming	
Color Consistency	<6	Dimmable	Yes
Color Rendering Index (Nom)	90		
LLMF At End Of Nominal Lifetime (Nom)	70 %		

# MASTER VALUE LEDspot MV

## Approval and Application


Energy Efficiency Label (EEL)	A+
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	5 kWh

## Product Data

Full product code	871869670731900
Order product name	Master LED 4.9-50W GU10 927 36D Dim

EAN/UPC - Product	8718696707319
Order code	929001348808
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001348808
Net Weight (Piece)	0.038 kg


## Dimensional drawing



GU10 230V5W-50W 345lm 36D 2700K GU10 Dim


Product	D	C
Master LED 4.9-50W GU10 927 36D Dim	50 mm	54 mm

## Photometric data



© 2020 Philips Lighting B.V. All rights reserved.

MASTER LEDspotMV 50W GU10 927 36D 355lm




MASTER LEDspotMV 35W GU10 927 36D 260lm



MASTER LEDspotMV 50W GU10 36D 355lm

# MASTER VALUE LEDspot MV

## Lifetime



MASTER LEDspotMV GU10 922-927 36D

MASTER LEDspotMV GU10 922-927 36D

