

**PHILIPS**

Eco passport

## MAS LED spot VLE D 4.9-50W GU10 930 36D MASTER LEDspot 230V

Delivering a warm, halogen-like accent beam, MASTER LEDspot MV is a perfect fit for spot lighting (track, corridors, lift lobbies, display cases and cabinets) in the hospitality industry. It is particularly suitable to public areas where the light is on 24/7, such as lobbies, corridors, stairwells. MASTER LEDspot MV delivers huge energy savings and minimizes maintenance cost without any compromise on brightness, enabling hospitality owners to achieve a return on their investment within one year. These LEDspots are compatible with most existing fixtures with a GU10 holder and designed as a retrofit replacement for halogen or incandescent spots. The dimmable versions drive further efficiencies, while helping to create the desired atmosphere.



### Our Eco passport



#### Etykieta

- Funkcja ściemniania: tak
- Etykieta Efektywności Energetycznej (EEL): A+
- Skuteczność świetlna (znamionowa) (Nom): 82,65 lm/W
- Power (Rated) (Nom): 4.9 W



#### Obieg

- Trwałość nominalna (Nom): 25000 h



#### Opakowanie

- SAP Weight Paper Unit (Case): 0,230 kg
- SAP Weight Paper Unit (Piece): 0,012 kg



#### Substancje

- Zgodność z normą UE RoHS: No



#### Masa i materiały

- Waga netto (szt.): 0,038 kg

Energy efficiency ranking / External awards

