



# MASTER VALUE LEDspot MV

## MAS LED spot VLE D 4.9-50W GU10 930 36D

Delivering a warm, halogen-like accent beam, MASTER VALUE is a perfect fit for spot lighting. Thanks to its high CRI, it realizes more natural colors, creating cozy and comfortable ambiances for residential and hospitality projects, and emphasizing the beauty of merchandise in retail. These LED spots MV GU10 have the familiar look and feel of spot lamps, keeping the classic beauty of glass spots and adding the strong performance of LED technology. The dimming function enables you to create the atmosphere you desire, and it works with broad selection of dimmers. MASTER VALUE also offers more energy savings than normal LED spots.

### Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

### Product data


General Information	
Cap-Base	GU10 [GU10]
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
Flux measurement reference	Narrow Cone
CE mark	Yes
EU RoHS compliant	Yes
Light Technical	
Color Code	930 [CCT of 3000K]

Beam Angle (Nom)	36 degree(s)
Luminous Flux	365 lm
Luminous Intensity (Nom)	650 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	82 lm/W
Color Consistency	<6
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	365 lm
Flickering value (PstLM)	1

# MASTER VALUE LEDspot MV

Stroboscopic effect value (SVM)	0.4
Photobiological safety according to EN 62471 RG1	
<b>Operating and Electrical</b>	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	4.9 W
Lamp Current (Nom)	27 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.8
Voltage (Nom)	220-240 V
<b>Temperature</b>	
T-Case Maximum (Nom)	80 °C
<b>Controls and Dimming</b>	
Dimmable	Only with specific dimmers
<b>Mechanical and Housing</b>	
Bulb Shape	PAR16 [PAR 2 inch/50mm]

## Dimensional drawing




<b>Approval and Application</b>	
Energy Efficiency Class	F
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	5 kWh
EPREL Registration Number	391888
EyeComfort	Yes
<b>Product Data</b>	
Order product name	MAS LED spot VLE D 4.9-50W GU10 930 36D
Full product name	MAS LED spot VLE D 4.9-50W GU10 930 36D
Full product code	871869670787600
Order code	929001348902
Material Nr. (12NC)	929001348902
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696707876
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696707883


Product	D	C
MAS LED spot VLE D 4.9-50W GU10 930 36D	50 mm	54 mm

MASTER VALUE LEDspot MV

Photometric data



Accent Lighting Spots - MAS LED spot VLE D 4.9-50W GU10 930 36D




Spectral Power Distribution Colour - MAS LED spot VLE D 4.9-50W GU10 930 36D




Light Distribution Diagram - MAS LED spot VLE D 4.9-50W GU10 930 36D

Lifetime



Life Expectancy Diagram - MAS LED spot VLE D 4.9-50W GU10 930 36D



Lumen Maintenance Diagram - MAS LED spot VLE D 4.9-50W GU10 930 36D

## MASTER VALUE LEDspot MV

