



# MASTER VALUE LEDspot MV

## Master LED 5-50W GU10 930 36D Dim

Delivering a warm, halogen-like accent beam, MASTER VALUE LEDspot MV is a perfect for spot lighting. Thanks to its high CRI, it realizes more natural colors, enabling cozy and comfortable ambience for residential, hospitality and emphasize the beauty of merchandise in retail. These LEDspots have the familiar look and feel of glass spots, keeping the classic beauty of glass spots and adding the strong performance from LED technology. The dimming function enables to create the desired atmosphere and it works with broad selection of dimmers.

### Product data

General Information		Luminous Flux in 90° Cone (Rated)	
Cap-Base	GU10 [ GU10]		365 lm
EU RoHS compliant	Yes	Operating and Electrical	
Nominal Lifetime (Nom)	25000 h	Input Frequency	50 to 60 Hz
Switching Cycle	50000X	Power (Nom)	5 W
Technical Type	5-50W	Lamp Current (Nom)	27 mA
Light Technical		Wattage Equivalent	50 W
Color Code	930 [ CCT of 3000K]	Starting Time (Nom)	0.5 s
Beam Angle (Nom)	36 °	Warm Up Time to 60% Light (Nom)	0.5 s
Luminous Flux (Nom)	405 lm	Power Factor (Nom)	0.8
Luminous Intensity (Nom)	650 cd	Voltage (Nom)	220-240 V
Color Designation	White (WH)	Temperature	
Correlated Color Temperature (Nom)	3000 K	T-Case Maximum (Nom)	80 °C
Luminous Efficacy (rated) (Nom)	81.00 lm/W	Controls and Dimming	
Color Consistency	<6	Dimmable	Yes
Color Rendering Index (Nom)	90		
LLMF At End Of Nominal Lifetime (Nom)	70 %		

# MASTER VALUE LEDspot MV

## Approval and Application

Energy Efficiency Label (EEL)	A+
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	5 kWh


## Product Data

Full product code	871869675592100
Order product name	Master LED 5-50W GU10 930 36D Dim

EAN/UPC - Product	8718696755921
Order code	929001348908
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001348908
Net Weight (Piece)	0.038 kg

## Warnings and Safety


### Dimensional drawing




GU10 230V5W-50W 355lm 36D 3000K GU10 Dim

Product	D	C
Master LED 5-50W GU10 930 36D Dim	50 mm	54 mm

### Photometric data




MASTER LEDspotMV 50W GU10 930 36D 365lm



MASTER LEDspotMV 35W GU10 930 36D 270lm

# MASTER VALUE LEDspot MV

## Photometric data




MASTER LEDspotMV 50W GU10 36D 355lm

## Lifetime



MASTER LEDspotMV GU10 922-927 36D



MASTER LEDspotMV GU10 922-927 36D

