



MASTER VALUE LEDspot MV

MASTER LED spot VLE D 7-80W GU10 840 36D

Delivering a warm, halogen-like accent beam, MASTER VALUE is a perfect fit for spot lighting. Thanks to its high CRI, it realizes more natural colors, creating cozy and comfortable ambiances for residential and hospitality projects, and emphasizing the beauty of merchandise in retail. These LED spots MV GU10 have the familiar look and feel of spot lamps, keeping the classic beauty of glass spots and adding the strong performance of LED technology. The dimming function enables you to create the atmosphere you desire, and it works with broad selection of dimmers. MASTER VALUE also offers more energy savings than normal LED spots.

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

Product data

General Information	
Cap-Base	GU10 [GU10]
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	840 [CCT of 4000K]
Beam Angle (Nom)	36 degree(s)
Luminous Flux	610 lm

Luminous Intensity (Nom)	1,200 cd
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	87.14 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	610 lm
Operating and Electrical	
Line Frequency	50 to 60 Hz

MASTER VALUE LEDspot MV

Input Frequency	50 to 60 Hz
Power Consumption	7 W
Lamp Current (Nom)	35 mA
Wattage Equivalent	80 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.8
Voltage (Nom)	220-240 V

Temperature

T-Case Maximum (Nom)	85 °C
----------------------	-------

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Bulb Shape	PAR16 [PAR 2 inch/50mm]
------------	-------------------------


Approval and Application

Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	7 kWh
EyeComfort	Yes

Product Data



Order product name	MAS LED spot VLE D 7-80W GU10 840 36D
Full product name	MASTER LED spot VLE D 7-80W GU10 840 36D
Full product code	871869670799900
Order code	70799900
Material Nr. (12NC)	929001349502
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696707999
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696708002

Dimensional drawing



Product	D	C
MAS LED spot VLE D 7-80W GU10 840 36D	50 mm	54 mm

Photometric data



Accent Lighting Spots - MAS LED spot VLE D 7-80W GU10 840 36D

Light Distribution Diagram - MAS LED spot VLE D 7-80W GU10 840 36D


MASTER VALUE LEDspot MV

Photometric data




Spectral Power Distribution Colour - MAS LED spot VLE D 7-80W GU10 840 36D

Lifetime



Life Expectancy Diagram - MAS LED spot VLE D 7-80W GU10 840 36D



Lumen Maintenance Diagram - MAS LED spot VLE D 7-80W GU10 840 36D

