



CorePro LEDspot Reflectors

CorePro LEDspotMV ND 4-42W 827 Refl63 CM

CorePro LEDspots Reflectors are a perfect fit for spot lighting and deliver warm halogen-like light. They are compatible with most existing fixtures with a GU10 or E27 base and are designed as a retrofit replacement for halogen or incandescent spots. CorePro LEDspots Reflectors deliver significant energy savings and minimize maintenance cost.

Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	120 degree(s)
Luminous Flux	505 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	126.25 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz


Input Frequency	50 to 60 Hz
Power Consumption	4 W
Lamp Current (Nom)	32 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.4
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	40 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	R63 [R 63mm]
Approval and Application	
Energy Consumption kWh/1000 h	4 kWh

CorePro LEDspot Reflectors

Product Data	
Order product name	CorePro LEDspotMV ND 4-42W 827 Refl63 CM
Full product name	CorePro LEDspotMV ND 4-42W 827 Refl63 CM
Full product code	871869676844000
Order code	929001350602
Material Nr. (12NC)	929001350602


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696768440
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696768457

Dimensional drawing



Product	D	C
CorePro LEDspotMV ND 4-42W 827 Refl63 CM	63 mm	102 mm


Photometric data



General Uniform Lighting
Page 10

General uniform lighting - CorePro LEDspotMV ND 4-42W 827 Refl63 CM

Light Distribution Diagram - CorePro LEDspotMV ND 4-42W 827 Refl63 CM




Spectral Power Distribution Colour - CorePro LEDspotMV ND 4-42W 827 Refl63 CM

CorePro LEDspot Reflectors

Lifetime



Life Expectancy Diagram - CorePro LEDspotMV ND 4-42W 827 Refl63 CM



Lumen Maintenance Diagram - CorePro LEDspotMV ND 4-42W 827 Refl63 CM

