



CorePro LED PLC

CorePro LED PLC CorePro LED PLC 4.5W 830 4P G24q-1

Philips CorePro LED PLC is the ideal uplamping solution for downlights in a wide range of general lighting applications. It integrates a LED light source into a traditional fluorescent form factor to offer superb energy savings over a lifetime that's twice as long as fluorescent alternatives.

Product data

General Information		Power Factor (Nom)		0.9
Cap-Base	G24Q-1 [G24q-1]	Voltage (Nom)		20-50 V
Nominal Lifetime (Nom)	30000 h	Temperature		
Switching Cycle	50000X	T-Ambient (Max)		35 °C
B50L70	30000 h	T-Ambient (Min)		-20 °C
Light Technical		T-Storage (Max)		65 °C
Colour Code	830 [CCT of 3000K]	T-Storage (Min)		-40 °C
Luminous Flux (Nom)	475 lm	T-Case Maximum (Nom)		60 °C
Luminous Flux (Rated) (Nom)	475 lm	Controls and Dimming		
Colour Temperature, horizontal (Nom)	3000 K	Dimmable		No
Color Consistency	<6	Mechanical and Housing		
Colour Rendering Index horiz (Nom)	83	Product Length		100 mm
LLMF At End Of Nominal Lifetime (Nom)	70 %	Approval and Application		
Operating and Electrical		Energy Efficiency Label		A+
Input Frequency	30000-80000 Hz	Energy Saving Product		Yes
Power (Rated) (Nom)	4.5 W	Approval Marks		TUV CE marking RoHS compliance KEMA Keur certificate
Lamp Current (Max)	260 mA			
Lamp Current (Min)	150 mA			
Starting Time (Nom)	0.5 s			
Warm Up Time to 60% Light (Nom)	0.5 s			

CorePro LED PLC


Energy Consumption kWh/1000 h	6 kWh
Product Data	
Full product code	871869670663300
Order product name	CorePro LED PLC CorePro LED PLC 4.5W 830 4P G24q-1
EAN/UPC - Product	8718696706633

Order code	70663300
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001351002
Net Weight (Piece)	0.075 kg

Warnings and Safety

- NOTES: The overall energy efficiency and light distribution of any installation that uses these lamps are determined by the design of the installation.



Dimensional drawing



Product	D1	D2	A1	A2	A3
CorePro LED PLC CorePro LED PLC 4.5W 830 4P G24q-1	24.3 mm	28.4 mm	95.8 mm	115 mm	130.6 mm

PLED PLC 24V 5-13W 450lm 3000K G24Q-1 ND

Photometric data




CorePro LED PLC 100mm 5W G24Q-1 830 475lm

LEDtube 100mm 5W G24Q-1 830 475lm


CorePro LED PLC

Photometric data




LEDtube 100mm 5W G24D-1

Lifetime



LEDtube 100mm 5W G24D-1



LEDtube 100mm 5W G24D-1

