



# CorePro LEDbulb

## CorePro LEDbulb D 8.5-60W A60 E27 827

LEDbulbs are compatible with existing fixtures with an E27 holder and are designed for retrofit replacement of incandescent bulbs.

### Product data


General Information	
Cap base	E27 [E27]
Nominal lifetime	15,000 h
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Colour Code	822-827 [tunable warm white]
Beam angle (nom.)	200 degree(s)
Luminous Flux	806 lm
Colour designation	Warm White (WW)
Luminous efficacy (rated) (nom.)	94.00 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	8.5 W
Lamp current (nom.)	45 mA
Wattage equivalent	60 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s

Power Factor (Fraction)	0.7
Voltage (nom.)	220-240 V
Temperature	
T-Case maximum (nom.)	85 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Lamp Finish	Frosted
Bulb shape	A60 [A 60 mm]
Approval and Application	
Energy consumption kWh/1,000 hours	9 kWh
Product Data	
Order product name	CorePro LEDbulb D 8.5-60W A60 E27 827
Full product name	CorePro LEDbulb D 8.5-60W A60 E27 827
Full EOC	871869676270700
Order code	76270700
Material no. (12 NC)	929001352502
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696762707
Numerator – packs per outer box	10

CorePro LEDbulb



EAN/UPC - Case	8718696762714
----------------	---------------

Dimensional drawing




Product	D	C
CorePro LEDbulb D 8.5-60W A60 E27 827	60 mm	110 mm

Photometric data



General uniform lighting - CorePro LEDbulb D 8.5-60W A60 E27 827

Spectral Power Distribution Colour - CorePro LEDbulb D 8.5-60W A60 E27 827



Light Distribution Diagram - CorePro LEDbulb D 8.5-60W A60 E27 827

CorePro LEDbulb

Lifetime



Life Expectancy Diagram - CorePro LEDbulb D 8.5-60W A60 E27 827



Lumen Maintenance Diagram - CorePro LEDbulb D 8.5-60W A60 E27 827

