



CorePro LEDlinear MV

CorePro LED linear D 14-120W R7S 118 830


CorePro R7S is a retrofit replacement for traditional double-ended linear R7S lamps. Its 'light all around' design delivers light that is just like a halogen lamp. Within the range, you can choose dimmable products which have deep a dimming function that enables a cosy ambience when using a dimmable fixture.

Product data

General Information		Temperature	
Cap base	R7S [R7s]	Warm-up time to 60% light (nom.)	0.5 s
Nominal lifetime (nom.)	15000 h	Power factor (nom.)	0.8
Switching cycle	50000X	Voltage (Nom)	220-240 V
Technical type	14-120W	Temperature	
Light Technical		T-Case maximum (nom.)	100 °C
Colour code	830 [CCT of 3,000 K]	Controls and Dimming	
Luminous flux (nom.)	2000 lm	Dimmable	Yes
Luminous flux (rated) (nom.)	2000 lm	Approval and Application	
Colour designation	White (WH)	Energy efficiency label (EEL)	A++
Correlated colour temperature (nom.)	3000 K	Energy Consumption kWh/1000 h	14 kWh
Luminous efficacy (rated) (nom.)	142.86 lm/W	Product Data	
Colour consistency	<6	Full product code	871869671400300
Color rendering index (nom.)	80	Order product name	CorePro LED linear D 14-120W R7S 118 830
LLMF at end of nominal lifetime (nom.)	70 %	EAN/UPC – product	8718696714003
Operating and Electrical		Order code	71400300
Input frequency	50 to 60 Hz	Numerator – quantity per pack	1
Power (Rated) (Nom)	14 W	Numerator – packs per outer box	10
Lamp current (nom.)	75 mA	Material no. (12NC)	929001353602
Wattage equivalent	120 W	Net weight (piece)	0.095 kg
Starting time (nom.)	0.5 s		

CorePro LEDlinear MV


Dimensional drawing



R7S 220V 15.5W-110W 1800lm 3000K R7S D



Product	D	C
CorePro LED linear D 14-120W R7S 118 830	29 mm	118 mm

Photometric data



General Lighting
T880 14W x 110mm (R7S) LED LINEAR
Page 17

CorePro LEDlinearMV 14-120W R7S 830 D



CorePro LEDlinear MV

Lifetime



LEDbulb 60W E14 827 FR B38



LEDbulb 60W E14 827 FR B38

