



CorePro LEDlinear MV



CorePro LED linear D 14-120W R7S 118 840

CorePro R7S is a retrofit replacement for traditional double-ended linear R7S lamps. Its ‘light all around’ design delivers light that is just like a halogen lamp. Within the range, you can choose dimmable products which have deep a dimming function that enables a cosy ambience when using a dimmable fixture.

Product data


General Information		Power Consumption	
Cap base	R7s	Lamp current (nom.)	14 W
Nominal lifetime	15,000 h	Wattage equivalent	75 mA
Switching Cycle	50,000	Starting time (nom.)	120 W
Lighting Technology	LED	Warm-up time to 60% light	0.5 s
CE mark	Yes	Power Factor (Fraction)	0.8
EU RoHS compliant	Yes	Voltage (nom.)	220-240 V
Light Technical		Temperature	
Colour Code	840 [CCT of 4000K]	T-Case maximum (nom.)	100 °C
Luminous Flux	2,000 lm	Controls and Dimming	
Colour designation	Cool White (CW)	Dimmable	Yes
Correlated Colour Temperature	4000 K	Mechanical and Housing	
Luminous efficacy (rated) (nom.)	142.86 lm/W	Bulb shape	Linear
Colour consistency	<6	Approval and Application	
Colour rendering index (CRI)	80	Energy Efficiency Class	D
LLMF at end of nominal lifetime (nom.)	70 %	Energy consumption kWh/1,000 hours	14 kWh
Flickering value (PstLM)	1	EPREL registration number	397583
Stroboscopic effect	0.4	EyeComfort	Yes
Operating and Electrical			
Line Frequency	50 to 60 Hz		
Input frequency	50 to 60 Hz		

CorePro LEDlinear MV

Application Conditions	
Can it be used in closed luminaires	No
Product Data	
Order product name	CorePro LED linear D 14-120W R7S 118 840
Full product name	CorePro LED linear D 14-120W R7S 118 840
Full EOC	871869671406500
Order code	71406500


Material no. (12 NC)	929001353702
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696714065
Numerator – packs per outer box	10
EAN/UPC – Case	8718696714072

Dimensional drawing




Product	D	C
CorePro LED linear D 14-120W R7S 118 840	29 mm	118 mm


Photometric data



Spectral Power Distribution Colour - CorePro LED linear D 14-120W R7S 118 840



General uniform lighting - CorePro LED linear D 14-120W R7S 118 840




Light Distribution Diagram - CorePro LED linear D 14-120W R7S 118 840

Lifetime



Life Expectancy Diagram - CorePro LED linear D 14-120W R7S 118 840



Lumen Maintenance Diagram - CorePro LED linear D 14-120W R7S 118 840

