



MASTER LEDspot PAR High Lumen

Master LED PAR30L 32W 15D 830

Philips High Lumen PAR30L integrates a leading COB LED light source and a compact high efficiency driver into a traditional CDM PAR30L form-factor. It brings out the beauty in merchandise with brighter, high performance lighting. Additionally, the lamp features an over temperature protection (OTP) to ensure a long operating life time.

Product data


General Information			
Cap-Base	E27	Input Frequency	50 to 60 Hz
Nominal lifetime	25,000 hour(s)	Power Consumption	32 W
Switching Cycle	50,000	Lamp Current (Nom)	160 mA
Lighting Technology	LED	Wattage Equivalent	50 W
EU RoHS compliant	Yes	Starting Time (Nom)	0.5 s
		Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.9
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	830 [CCT of 3000K]	T-Case Maximum (Nom)	79 °C
Beam Angle (Nom)	15 degree(s)		
Luminous Flux	3,000 lm	Controls and Dimming	
Color Designation	White (WH)	Dimmable	No
Correlated Color Temperature (Nom)	3000 K		
Luminous Efficacy (rated) (Nom)	93.00 lm/W	Mechanical and Housing	
Color Consistency	<6	Bulb Shape	PAR30L
Color rendering index (CRI)	82		
LLMF At End Of Nominal Lifetime (Nom)	70 %	Approval and Application	
		Suitable For Accent Lighting	Yes
Operating and Electrical			
Line Frequency	50 to 60 Hz		

MASTER LEDspot PAR High Lumen

Energy Consumption kWh/1000 h	32 kWh
Product Data	
Order product name	Master LED PAR30L 32W 15D 830
Full product name	Master LED PAR30L 32W 15D 830
Full product code	871869673138300
Order code	73138300



Material Nr. (12NC)	929001354308
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696731383
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696731390

Dimensional drawing




Product	D	C
Master LED PAR30L 32W 15D 830	95.5 mm	129 mm

Photometric data



Spectral Power Distribution Colour - Master LED PAR30L 32W 15D 830


Accent Lighting Spots - Master LED PAR30L 32W 15D 830




Light Distribution Diagram - Master LED PAR30L 32W 15D 830

MASTER LEDspot PAR High Lumen

Lifetime



Life Expectancy Diagram - Master LED PAR30L 32W 15D 830



Lumen Maintenance Diagram - Master LED PAR30L 32W 15D 830

