



MASTER LEDspot PAR High Lumen

Master LED PAR30L 32W 15D 830

Philips High Lumen PAR30L integrates a leading COB LED light source and a compact high-efficiency driver into a traditional CDM PAR30L form-factor. It brings out the beauty in merchandise with brighter, high-performance lighting. Additionally, the lamp features an over temperature protection (OTP) to ensure a long operating life time.

Product data

General Information	
Cap base	E27 [E27]
Nominal lifetime (nom.)	25000 h
Switching cycle	50000X
Technical type	32-50W
Light Technical	
Colour Code	830 [CCT of 3,000 K]
Beam Angle (Nom)	15 °
Lamp Luminous Flux 25°C EL (Nom)	3000 lm
Lamp Luminous Flux (Nom)	3000 lm
Luminous intensity (nom.)	26000 cd
Colour Designation	White (WH)
Rated beam angle	15 °
Colour Temperature, horizontal (Nom)	3000 K
Lamp Luminous Efficacy EM (Nom)	93.00 lm/W
Colour consistency	<6
Colour Rendering Index,horiz (Nom)	82
LLMF at end of nominal lifetime (nom.)	70 %


Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	32 W
Lamp current (nom.)	160 mA
Wattage equivalent	50 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.9
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	79 °C
Controls and Dimming	
Dimmable	No
Approval and Application	
Energy efficiency label (EEL)	A+
Suitable for accent lighting	Yes

MASTER LEDspot PAR High Lumen

Energy Consumption kWh/1000 h	32 kWh
Product Data	
Full product code	871869673138300
Order product name	Master LED PAR30L 32W 15D 830
EAN/UPC – product	8718696731383
Order code	929001354308

Numerator – quantity per pack	1
Numerator – packs per outer box	6
Material no. (12NC)	929001354308
Net weight (piece)	0.410 kg



Dimensional drawing




PAR30L 220-240V 32-70W 15D 3000K E27 ND

Product	D	C
Master LED PAR30L 32W 15D 830	95.5 mm	129 mm

Photometric data




LEDspot PAR30L E27 3000K 15D



MASTER LEDspot PAR High Lumen

Lifetime



LEDspot MAS 37W E27 PAR30L 830 15D ND

LEDspot MAS 37W E27 PAR30L 830 15D ND

