



CorePro Plastic LEDbulbs

LEDBulb 14.5W E27 3000K 230V A67 APR

CorePro LEDbulbs are compatible with existing fixtures with an E27 or B22 holder and are designed for retrofit replacement of incandescent bulbs. They deliver huge energy savings and minimize maintenance cost.

Product data


General Information			
Cap-Base	E27 [E27]	Power Consumption	14.5 W
Nominal lifetime	10,000 hour(s)	Lamp Current (Nom)	130 mA
Switching Cycle	50,000	Wattage Equivalent	120 W
Lighting Technology	LED	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.5
		Voltage (Nom)	220-240 V
Light Technical			
Color Code	730 [CCT of 3000K]	Temperature	
Beam Angle (Nom)	150 degree(s)	T-Case Maximum (Nom)	90 °C
Luminous Flux	1,700 lm		
Color Designation	White (WH)	Controls and Dimming	
Correlated Color Temperature (Nom)	3000 K	Dimmable	No
Luminous Efficacy (rated) (Nom)	117.00 lm/W		
Color Consistency	<6	Mechanical and Housing	
Color rendering index (CRI)	70	Bulb Finish	Frosted
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Shape	A67 [A 67mm]
Operating and Electrical		Product Data	
Line Frequency	50 to 60 Hz	Order product name	LEDBulb 14.5W E27 3000K 230V A67 APR
Input Frequency	50 to 60 Hz	Full product name	LEDBulb 14.5W E27 3000K 230V A67 APR

CorePro Plastic LEDbulbs

Full product code	871869671540600
Order code	71540600
Material Nr. (12NC)	929001355008
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696715406


Numerator - Packs per outer box	6
EAN/UPC - Case	8718696715413

Dimensional drawing




Product	D	C
LEDBulb 14.5W E27 3000K 230V A67 APR	68 mm	132 mm


Photometric data



Spectral Power Distribution Colour - LEDBulb 14.5W E27 3000K 230V A67 APR




General uniform lighting - LEDBulb 14.5W E27 3000K 230V A67 APR




Light Distribution Diagram - LEDBulb 14.5W E27 3000K 230V A67 APR

CorePro Plastic LEDbulbs

Lifetime



Life Expectancy Diagram - LEDBulb 14.5W E27 3000K 230V A67 APR



Lumen Maintenance Diagram - LEDBulb 14.5W E27 3000K 230V A67 APR

