



CorePro LEDbulbs

LEDBulb 40W E27 6500K 230V A130 APR

Product data

General Information	
Cap base	E27 [E27]
RoHS mark	RoHS mark
Nominal lifetime (nom.)	10000 h
Switching cycle	50000X
Technical type	40-75W

Light Technical	
Colour Code	765 [CCT of 6500K]
Technical Beam Angle (Nom)	150 °
Lamp Luminous Flux 25°C EL (Nom)	5000 lm
Lamp Luminous Flux (Nom)	5000 lm
Colour Designation	Cool Daylight
Colour Temperature, horizontal (Nom)	6500 K
Lamp Luminous Efficacy EM (Nom)	125.00 lm/W
Colour consistency	<6
Colour Rendering Index, horiz (Nom)	70
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	40 W
Lamp current (nom.)	340 mA
Wattage equivalent	75 W
Starting time (nom.)	0.5 s

Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.5
Voltage (Nom)	220-240 V

Temperature	
T-Case maximum (nom.)	90 °C


Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb finish	Frosted (FR)

Product Data	
Full product code	871869671550500
Order product name	LEDBulb 40W E27 6500K 230V A130 APR
EAN/UPC – product	8718696715505
Order code	929001355808
Numerator – quantity per pack	1
Numerator – packs per outer box	6
Material no. (12NC)	929001355808
Net weight (piece)	0.292 kg

CorePro LEDbulbs




Dimensional drawing



A130 220-240V 40-75W 6500K E27 ND

Product	D	C
LEDBulb 40W E27 6500K 230V A130 APR	130 mm	225 mm

Photometric data



Technical Parameters 41 Page Lighting 41 Page 11

A130 40-75W E27 230V

CorePro LEDbulbs

Lifetime

