



TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL)

TForce LED HPI ND 200-145W E40 840 60D

Philips TrueForce LED Industrial and Retail lamps give you a quick and easy payback solution to replace HID lamps in High-bay applications. The solution gives you the LED benefits of energy-efficiency and long-lifetime, plus the initial investment is low. With unique lamp design and compatibility, you can directly retrofit HID lamps with TrueForce LED lamps without changing the fixtures or gear. Multiple beam angle options and high colour-rendering index enhance the lighting distribution while creating a comfortable, safe and high-productivity environment.

Warnings and Safety

• EM version requires an EM ballast to operate. Please refer to the installation guide or consult a Philips Lighting representative.

Product data

General Information			
Cap-Base	E40 [E40]	Luminous Flux	20,000 lm
Nominal lifetime	50,000 hour(s)	Color Designation	Cool White (CW)
Switching Cycle	50,000	Correlated Color Temperature (Nom)	4000 K
Lighting Technology	LED	Luminous Efficacy (rated) (Nom)	137.00 lm/W
EU RoHS compliant	Yes	Color Consistency	<6
		Color rendering index (CRI)	80
		LLMF At End Of Nominal Lifetime (Nom)	70 %
Light Technical		Operating and Electrical	
Color Code	840 [CCT of 4000K]	Line Frequency	50 Hz
Beam Angle (Nom)	60 degree(s)		

TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL)

Input Frequency	50 Hz
Power Consumption	145 W
Lamp Current (Nom)	3,900 mA
Starting Time (Nom)	0.7 s
Warm-up time to 60% light	0.7 s
Power Factor (Fraction)	0.7
Voltage (Nom)	100-145 V

Temperature

T-Case Maximum (Nom)	95 °C
----------------------	-------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Shape	Others
------------	--------


Approval and Application

Energy Consumption kWh/1000 h	160 kWh
-------------------------------	---------

Product Data


Order product name	TForce LED HPI ND 200-145W E40 840 60D
Full product name	TForce LED HPI ND 200-145W E40 840 60D
Full product code	871869671386000
Order code	929001357002
Material Nr. (12NC)	929001357002
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696713860
Numerator - Packs per outer box	2
EAN/UPC - Case	8718696713877

Dimensional drawing




Product	D	C
TForce LED HPI ND 200-145W E40 840 60D	210 mm	250 mm

Photometric data



General Uniform Lighting - TForce LED HPI ND 200-145W E40 840 60D



Light Distribution Diagram - TForce LED HPI ND 200-145W E40 840 60D


TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL)

Photometric data




Spectral Power Distribution Colour - TForce LED HPI ND 200-145W E40 840 60D


Lifetime



Life Expectancy Diagram - TForce LED HPI ND 200-145W E40 840 60D



Lumen Maintenance Diagram - TForce LED HPI ND 200-145W E40 840 60D



Life Expectancy Diagram - TForce LED HPI ND 200-145W E40 840 60D

TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL)

