



TrueForce LED 工业和零售（高棚灯 – HPI/SON/HPL）

TForce LED HPI ND 200-145W E40 840 120D

飞利浦 TrueForce LED 工业和零售灯为您提供可轻松迅速获取回报的解决方案，用来替换高棚灯应用中的 HID 灯。此解决方案可为您带来 LED 的能效和长寿命效益，而且只需低初始投资。利用独特的灯设计和兼容性，您可以直接用 TrueForce LED 灯来改造 HID 灯，无需修改灯具或装置。多种光束角度选项和高显色指数可增强照明分布，同时创造舒适、安全且高产的环境。

安全提示

• EM 型号需要 EM 镇流器才能工作。请参阅安装指南或咨询飞利浦照明代表。

产品数据


一般信息		颜色一致性	
底座	E40 [E40]	显色指数 (CRI)	<6
标称使用寿命	50,000 小时	标称使用寿命结束时灯的光通维持率 (标称)	80
切换循环	50,000		70 %
照明技术	LED	操作和电气	
符合欧盟 RoHS 规范	是	线频率	50 Hz
		输入频率	50 Hz
		功耗	145 W
		灯具电流 (标称)	3,900 mA
		启动时间 (标称)	0.7 s
		60% 灯光下的预热时间	0.7 s
		功率系数 (小数)	0.7
		电压 (标称)	100-145 V
灯技术			
颜色代码	840 [CCT of 4000K]		
光束角度 (标称)	120 °		
光通量	20,000 lm		
颜色名称	冷白色 (CW)		
相关色温 (标称)	4000 K		
光效 (额定) (标称)	137.00 lm/W		

TrueForce LED 工业和零售 (高棚灯 – HPI/SON/HPL)

温度	
最大外壳温度 (标称)	95 °C
控制和调光	
可调光	否
机械和外壳	
灯泡外形	其他
审批和申请	
能耗 kWh/1000 h	160 kWh



产品数据	
订单产品名称	TForce LED HPI ND 200-145W E40 840 120D
完整的产品名称	TForce LED HPI ND 200-145W E40 840 120D
完整产品代码	871869671388400
订购代码	929001357102
材料编号 (12NC)	929001357102
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8718696713884
计算器 - 每个外包装箱中的包数	2
EAN/UPC - 案例	8718696713891

二维绘图



Product	D	C
TForce LED HPI ND 200-145W E40 840 120D	210 mm	250 mm

光度数据



General uniform lighting - TForce LED HPI ND 200-145W E40 840 120D

Light Distribution Diagram - TForce LED HPI ND 200-145W E40 840 120D


TrueForce LED 工业和零售 (高棚灯 – HPI/SON/HPL)

光度数据




Spectral Power Distribution Colour - TForce LED HPI ND 200-145W E40 840 120D


寿命



Life Expectancy Diagram - TForce LED HPI ND 200-145W E40 840 120D



Lumen Maintenance Diagram - TForce LED HPI ND 200-145W E40 840 120D



Life Expectancy Diagram - TForce LED HPI ND 200-145W E40 840 120D

TrueForce LED 工业和零售 (高棚灯 – HPI/SON/HPL)

