



T8

16.5T8PRO/48-835/BB20/G 10/1 FB

Our TLEDs are available in InstantFit (Type A / Type C) or MainsFit (Ballast bypass / Type B) versions. The InstantFit lamps work on a broad variety of ballasts and LED drivers. Only InstantFit has over 15,000 lamp & ballast combinations delivering even light output, energy savings and a long lifetime. Our MainsFit products feature a double-ended design, simplifying installation while a proprietary safety circuit minimizes a shock risk. Lamp sizes range from 2-foot to 8-foot and U-bend with a variety of lumen outputs.

Product data

General Information		Input Frequency	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Input Frequency	50 to 60 Hz
Nominal lifetime	50,000 hour(s)	Power Consumption	16.5 W
Switching Cycle	50,000	Lamp Current (Max)	154 mA
Lighting Technology	LED	Lamp Current (Min)	55 mA
EU RoHS compliant	Yes	Starting Time (Nom)	0.5 s
		Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.9
		Voltage (Nom)	120-277 V
Light Technical		Temperature	
Color Code	835 [CCT of 3500K]	Ambient temperature range	-20 °C to 45 °C
Beam Angle (Nom)	240 degree(s)	T-Case Maximum (Nom)	70 °C
Luminous Flux	2,000 lm		
Color Designation	White (WH)	Controls and Dimming	
Correlated Color Temperature (Nom)	3500 K	Dimmable	No
Luminous Efficacy (rated) (Nom)	121.00 lm/W		
Color Consistency	<6	Mechanical and Housing	
Color rendering index (CRI)	80	Product Length	1,200 mm
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Shape	Tube, double-ended
Operating and Electrical			
Line Frequency	50 to 60 Hz		

T8

Approval and Application


Energy Saving Product	Yes
Approval Marks	UL certificate RoHS compliance DLC compliance
Energy Consumption kWh/1000 h	- kWh
Energy Certifications	DLC Standard

Product Data

Order product name	16.5T8PRO/48-835/BB20/G 10/1 FB
--------------------	---------------------------------



Full product name	16.5T8PRO/48-835/BB20/G 10/1 FB
Order code	929001363234
Material Nr. (12NC)	929001363234
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677471750
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677471755

Dimensional drawing




Product	D1	D2	A1	A2	A3
16.5T8PRO/48-835/BB20/G 10/1 FB	25.7 mm	26 mm	1,200 mm	1,207 mm	1,214 mm

Photometric data





General uniform lighting - 16.5T8PRO/48-835/BB20/G 10/1 FB

Light Distribution Diagram - 16.5T8PRO/48-835/BB20/G 10/1 FB




Spectral Power Distribution Colour - 16.5T8PRO/48-835/BB20/G 10/1 FB


Lifetime




Life Expectancy Diagram - 16.5T8PRO/48-835/BB20/G 10/1 FB



Life Expectancy Diagram - 16.5T8PRO/48-835/BB20/G 10/1 FB



Life Expectancy Diagram - 16.5T8PRO/48-835/BB20/G 10/1 FB



Lumen Maintenance Diagram - 16.5T8PRO/48-835/BB20/G 10/1 FB

Lumen Maintenance Diagram - 16.5T8PRO/48-835/BB20/G 10/1 FB

