



# T8

## 16.5T8/COR/48-840/MF21/G 10/1

Our TLEDs are available in InstantFit (Type A / Type C) or MainsFit (Ballast bypass / Type B) versions. The InstantFit lamps work on a broad variety of ballasts and LED drivers. Only InstantFit has over 15,000 lamp & ballast combinations delivering even light output, energy savings and a long lifetime. Our MainsFit products feature a double-ended design, simplifying installation while a proprietary safety circuit minimizes a shock risk. Lamp sizes range from 2-foot to 8-foot and U-bend with a variety of lumen outputs.

### Product data

General Information		Starting Time (Nom)	
Base	G13 [ Medium Bi-Pin Fluorescent]		0.5 s
EU RoHS compliant	Yes	Warm Up Time to 60% Light (Nom)	0.5 s
Nominal Lifetime (Nom)	50000 h	Power Factor (Nom)	0.9
Switching Cycle	50000X	Voltage (Nom)	120-277 V
Light Technical		Temperature	
Color Code	841 [ CCT of 4100K (841)]	T-Ambient (Max)	45 °C
Beam Angle (Nom)	240 °	T-Ambient (Min)	-20 °C
Initial lumen (Nom)	2100 lm	T-Storage (Max)	65 °C
Correlated Color Temperature (Nom)	4000 K	T-Storage (Min)	-40 °C
Color Consistency	<6	T-Case Maximum (Nom)	70 °C
Color Rendering Index (Nom)	80	Controls and Dimming	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Dimmable	No
Operating and Electrical		Mechanical and Housing	
Input Frequency	50 to 60 Hz	Product Length	1200 mm
Power (Rated) (Nom)	16.5 W	Approval and Application	
Lamp Current (Max)	154 mA	Energy Saving Product	Yes
Lamp Current (Min)	55 mA		

# T8

<b>Approbation Marks</b>	RoHS compliance UL certificate DLC compliance
<b>Product Data</b>	
<b>Order product name</b>	16.5T8/COR/48-840/MF21/G 10/1
<b>EAN/UPC - Product</b>	046677471767
<b>Order code</b>	471763

<b>Numerator - Quantity Per Pack</b>	1
<b>Numerator - Packs per outer box</b>	10
<b>Material Nr. (12NC)</b>	929001363364
<b>Net Weight (Piece)</b>	0.215 kg
<b>Model Number</b>	9290013633B



## Dimensional drawing

A3


Product	D1	D2	A1	A2	A3
16.5T8/COR/48-840/MF21/G	25.7 mm	26 mm	1200 mm	1207 mm	1214 mm
10/1					

### TLED IF CorePro 4ft 2100lm 4000K

## Photometric data





### LEDtube 16.5 W, 840, G13, T8, UHO



### Mains DLC 120-277V 17W 2100lm 4000K ND



### Mains DLC 17W 2000-2100lm 3000\_5000K ND

Lifetime




Mains DLC 17W 2000-2100lm 3000\_5000K ND

Mains DLC 17W 2000-2100lm 3000\_5000K ND



Mains DLC 17W 2000-2100lm 3000\_5000K ND

Mains DLC 17W 2000-2100lm 3000 5000K ND



Mains DLC 17W 2000-2100lm 3000 5000K ND

