



CorePro LEDspot MV

CorePro LEDspot 4-35W GU10 840 36D DIM

CorePro LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. They are compatible with most existing fixtures with a GU10 or E14 holder and are designed as a retrofit replacement for halogen or incandescent spots. LEDlamps deliver huge energy savings and minimize maintenance cost.

Product data

General Information	
Cap base	GU10 [GU10]
RoHS mark	RoHS mark
Nominal lifetime (nom.)	15000 h
Switching cycle	50000X
Technical type	4-35W
Light Technical	
Colour code	840 [CCT of 4,000 K]
Beam Angle (Nom)	36 °
Luminous flux (nom.)	270 lm
Luminous flux (rated) (nom.)	270 lm
Luminous intensity (nom.)	540 cd
Colour designation	Cool White (CW)
Rated beam angle	36 °
Correlated colour temperature (nom.)	4000 K
Luminous efficacy (rated) (nom.)	67.00 lm/W
Colour consistency	<6
Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %
Luminous Flux in 90° Cone (Rated)	270 lm

Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	4 W
Lamp current (nom.)	19 mA
Wattage equivalent	35 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.7
Voltage (Nom)	220-240 V

Temperature	
T-Case maximum (nom.)	65 °C

Controls and Dimming	
Dimmable	Yes

Approval and Application	
Energy efficiency label (EEL)	A+
Suitable for accent lighting	Yes
Energy Consumption kWh/1000 h	4 kWh


Product Data	
Full product code	871869673022500

CorePro LEDspot MV

Order product name	CorePro LEDspot 4-35W GU10 840 36D DIM
EAN/UPC – product	8718696730225
Order code	73022500
Numerator – quantity per pack	1
Numerator – packs per outer box	10

Material no. (12NC)	929001364002
Net weight (piece)	0.038 kg


Dimensional drawing




GU10 230V 4-35W 270lm 36D 4000K GU10 D

Product	D	C
CorePro LEDspot 4-35W GU10 840 36D DIM	50 mm	54 mm


Photometric data



Classic LEDspotMV 35W GU10 840 36D





CorePro LEDspotMV 35W GU10 830 36D CLA



CorePro LEDspotMV 25W GU10 840 36D

CorePro LEDspot MV

Lifetime



CLA LEDspotMV 50W GU10 827 36D ND

CLA LEDspotMV 50W GU10 827 36D ND

