



CorePro LEDspot MV

CorePro LEDspot 5-50W GU10 840 36D DIM

CorePro LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. They are compatible with most existing fixtures with a GU10 or E14 holder and are designed as a retrofit replacement for halogen or incandescent spots. LEDlamps deliver huge energy savings and minimize maintenance cost.

Product data

General Information	
Cap base	GU10 [GU10]
Nominal lifetime	15,000 h
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Colour Code	840 [CCT of 4000K]
Beam angle (nom.)	36 degree(s)
Luminous Flux	380 lm
Luminous intensity (nom.)	710 cd
Colour designation	Cool White (CW)
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	76.00 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %
Luminous flux in 90° cone (rated)	380 lm
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz


Power Consumption	5 W
Lamp current (nom.)	25 mA
Wattage equivalent	50 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (nom.)	220-240 V
Temperature	
T-Case maximum (nom.)	65 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb shape	PAR16 [PAR 2 inch/50 mm]
Approval and Application	
Suitable for accent lighting	Yes
Energy consumption kWh/1,000 hours	5 kWh
EyeComfort	Yes

CorePro LEDspot MV

Product Data	
Order product name	CorePro LEDspot 5-50W GU10 840 36D DIM
Full product name	CorePro LEDspot 5-50W GU10 840 36D DIM
Full EOC	871869673024900
Order code	73024900
Material no. (12 NC)	929001364302



SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696730249
Numerator – packs per outer box	10
EAN/UPC – Case	8718696730256

Dimensional drawing




Product	D	C
CorePro LEDspot 5-50W GU10 840 36D DIM	50 mm	54 mm

Photometric data



Accent Lighting Spots - CorePro LEDspot 5-50W GU10 840 36D DIM


Light Distribution Diagram - CorePro LEDspot 5-50W GU10 840 36D DIM




Spectral Power Distribution Colour - CorePro LEDspot 5-50W GU10 840 36D DIM

CorePro LEDspot MV

Lifetime



Life Expectancy Diagram - CorePro LEDspot 5-50W GU10 840 36D DIM



Lumen Maintenance Diagram - CorePro LEDspot 5-50W GU10 840 36D DIM

