



MASTER LEDspot PAR High Lumen

Master LED PAR30L 40W 30D 857

Philips High Lumen PAR30L integrates a leading COB LED light source and a compact high efficiency driver into a traditional CDM PAR30L form-factor. It brings out the beauty in merchandise with brighter, high performance lighting. Additionally, the lamp features an over temperature protection (OTP) to ensure a long operating life time.

Product data


General Information		Operating and Electrical	
Cap-Base	E27 [E27]	Line Frequency	50 to 60 Hz
Nominal lifetime	25,000 hour(s)	Input Frequency	50 to 60 Hz
Switching Cycle	50,000	Power Consumption	40 W
Lighting Technology	LED	Lamp Current (Nom)	196 mA
EU RoHS compliant	Yes	Wattage Equivalent	70 W
Light Technical		Starting Time (Nom)	0.5 s
Color Code	857 [CCT of 5700K]	Warm-up time to 60% light	0.5 s
Beam Angle (Nom)	30 degree(s)	Power Factor (Fraction)	0.9
Luminous Flux	4,600 lm	Voltage (Nom)	220-240 V
Luminous Intensity (Nom)	14,000 cd	Temperature	
Color Designation	Daylight	T-Case Maximum (Nom)	90 °C
Correlated Color Temperature (Nom)	5700 K	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	115.00 lm/W	Dimmable	No
Color Consistency	<6	Mechanical and Housing	
Color rendering index (CRI)	82	Bulb Shape	PAR30L [PAR 3.75 inch/95mm Long]
LLMF At End Of Nominal Lifetime (Nom)	70 %		

MASTER LEDspot PAR High Lumen

Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	40 kWh
Product Data	
Order product name	Master LED PAR30L 40W 30D 857
Full product name	Master LED PAR30L 40W 30D 857
Full product code	871869675947900


Order code	929001375008
Material Nr. (12NC)	929001375008
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696759479
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696759486

Dimensional drawing




Product	D	C
Master LED PAR30L 40W 30D 857	95.5 mm	129 mm

Photometric data




Light Distribution Diagram - Master LED PAR30L 40W 30D 857




Spectral Power Distribution Colour - Master LED PAR30L 40W 30D 857

MASTER LEDspot PAR High Lumen

Lifetime



Lumen Maintenance Diagram - Master LED PAR30L 40W 30D 857



Life Expectancy Diagram - Master LED PAR30L 40W 30D 857

